





THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN R BROWN	190C12065	 TE Connectivity	
		GW J GESFORD			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J GESFORD	190C12065	NAME
 FINISH  SEE TABLE		PRODUCT SPEC	HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED		
		APPLICATION SPEC			
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	WEIGHT	A1 00779 C= 146492			
CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 2 REV B

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOCAD

DIST00

REV

DATE

BY

APPROVED

DESCRIPTION

SEE SHEET 1

△₆	101.19 [3.984]	99.06 [3.900]	39	80	9-146492-0
△₆	98.65 [3.884]	96.52 [3.800]	38	78	8-146492-9
△₆	96.11 [3.784]	93.98 [3.700]	37	76	8-146492-8
△₆	93.57 [3.684]	91.44 [3.600]	36	74	8-146492-7
△₆	91.03 [3.584]	88.90 [3.500]	35	72	8-146492-6
△₆	88.49 [3.484]	86.36 [3.400]	34	70	8-146492-5
△₆	85.95 [3.384]	83.82 [3.300]	33	68	8-146492-4
△₆	83.41 [3.284]	81.28 [3.200]	32	66	8-146492-3
△₆	80.87 [3.184]	78.74 [3.100]	31	64	8-146492-2
△₆	78.33 [3.084]	76.20 [3.000]	30	62	8-146492-1
△₆	75.79 [2.984]	73.66 [2.900]	29	60	8-146492-0
△₆	73.25 [2.884]	71.12 [2.800]	28	58	7-146492-9
△₆	70.71 [2.784]	68.58 [2.700]	27	56	7-146492-8
△₆	68.17 [2.684]	66.04 [2.600]	26	54	7-146492-7
△₆	65.63 [2.584]	63.50 [2.500]	25	52	7-146492-6
△₆	63.09 [2.484]	60.96 [2.400]	24	50	7-146492-5
△₆	60.55 [2.384]	58.42 [2.300]	23	48	7-146492-4
△₆	58.01 [2.284]	55.88 [2.200]	22	46	7-146492-3
△₆	55.47 [2.184]	53.34 [2.100]	21	44	7-146492-2
△₆	52.93 [2.084]	50.80 [2.000]	20	42	7-146492-1
△₆	50.39 [1.984]	48.26 [1.900]	19	40	7-146492-0
△₆	47.85 [1.884]	45.72 [1.800]	18	38	6-146492-9
△₆	45.31 [1.784]	43.18 [1.700]	17	36	6-146492-8
△₆	42.77 [1.684]	40.64 [1.600]	16	34	6-146492-7
△₆	40.23 [1.584]	38.10 [1.500]	15	32	6-146492-6
△₆	37.69 [1.484]	35.56 [1.400]	14	30	6-146492-5
△₆	35.15 [1.384]	33.02 [1.300]	13	28	6-146492-4
△₆	32.61 [1.284]	30.48 [1.200]	12	26	6-146492-3
△₆	30.07 [1.184]	27.94 [1.100]	11	24	6-146492-2
△₆	27.53 [1.084]	25.40 [1.000]	10	22	6-146492-1
△₆	24.99 [.984]	22.86 [.900]	9	20	6-146492-0
△₆	22.45 [.884]	20.32 [.800]	8	18	5-146492-9
△₆	19.91 [.784]	17.78 [.700]	7	16	5-146492-8
△₆	17.37 [.684]	15.24 [.600]	6	14	5-146492-7
△₆	14.83 [.584]	12.70 [.500]	5	12	5-146492-6
△₆	12.29 [.484]	10.16 [.400]	4	10	5-146492-5
△₆	9.75 [.384]	7.62 [.300]	3	8	5-146492-4
△₆	7.21 [.284]	5.08 [.200]	2	6	5-146492-3
△₆	4.67 [.184]	2.54 [.100]	1	4	5-146492-2
△₆	2.13 [.084]	-	-	2	5-146492-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

△₅	101.19 [3.984]	99.06 [3.900]	39	80	4-146492-0
△₅	98.65 [3.884]	96.52 [3.800]	38	78	3-146492-9
△₅	96.11 [3.784]	93.98 [3.700]	37	76	3-146492-8
△₅	93.57 [3.684]	91.44 [3.600]	36	74	3-146492-7
△₅	91.03 [3.584]	88.90 [3.500]	35	72	3-146492-6
△₅	88.49 [3.484]	86.36 [3.400]	34	70	3-146492-5
△₅	85.95 [3.384]	83.82 [3.300]	33	68	3-146492-4
△₅	83.41 [3.284]	81.28 [3.200]	32	66	3-146492-3
△₅	80.87 [3.184]	78.74 [3.100]	31	64	3-146492-2
△₅	78.33 [3.084]	76.20 [3.000]	30	62	3-146492-1
△₅	75.79 [2.984]	73.66 [2.900]	29	60	3-146492-0
△₅	73.25 [2.884]	71.12 [2.800]	28	58	2-146492-9
△₅	70.71 [2.784]	68.58 [2.700]	27	56	2-146492-8
△₅	68.17 [2.684]	66.04 [2.600]	26	54	2-146492-7
△₅	65.63 [2.584]	63.50 [2.500]	25	52	2-146492-6
△₅	63.09 [2.484]	60.96 [2.400]	24	50	2-146492-5
△₅	60.55 [2.384]	58.42 [2.300]	23	48	2-146492-4
△₅	58.01 [2.284]	55.88 [2.200]	22	46	2-146492-3
△₅	55.47 [2.184]	53.34 [2.100]	21	44	2-146492-2
△₅	52.93 [2.084]	50.80 [2.000]	20	42	2-146492-1
△₅	50.39 [1.984]	48.26 [1.900]	19	40	2-146492-0
△₅	47.85 [1.884]	45.72 [1.800]	18	38	1-146492-9
△₅	45.31 [1.784]	43.18 [1.700]	17	36	1-146492-8
△₅	42.77 [1.684]	40.64 [1.600]	16	34	1-146492-7
△₅	40.23 [1.584]	38.10 [1.500]	15	32	1-146492-6
△₅	37.69 [1.484]	35.56 [1.400]	14	30	1-146492-5
△₅	35.15 [1.384]	33.02 [1.300]	13	28	1-146492-4
△₅	32.61 [1.284]	30.48 [1.200]	12	26	1-146492-3
△₅	30.07 [1.184]	27.94 [1.100]	11	24	1-146492-2
△₅	27.53 [1.084]	25.40 [1.000]	10	22	1-146492-1
△₅	24.99 [.984]	22.86 [.900]	9	20	1-146492-0
△₅	22.45 [.884]	20.32 [.800]	8	18	146492-9
△₅	19.91 [.784]	17.78 [.700]	7	16	146492-8
△₅	17.37 [.684]	15.24 [.600]	6	14	146492-7
△₅	14.83 [.584]	12.70 [.500]	5	12	146492-6
△₅	12.29 [.484]	10.16 [.400]	4	10	146492-5
△₅	9.75 [.384]	7.62 [.300]	3	8	146492-4
△₅	7.21 [.284]	5.08 [.200]	2	6	146492-3
△₅	4.67 [.184]	2.54 [.100]	1	4	146492-2
△₅	2.13 [.084]	-	-	2	146492-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0

1

2

3

4

PLC

PLC

PLC

PLC

PLC

±

±

±

±

±

-

0.5[.02]

0.13[.005]

-

±

ANGLES

FINISH

SEE TABLE

MATERIAL

△₄

DWN
R BROWN
19OCT2006

CHK
J GESFORD
19OCT2006

APVD
J GESFORD
19OCT2006

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

HEADER ASSEMBLY, MOD II,
STACKING, DOUBLE ROW,
.025 SQ.POST, UNSHROUDED

A100779

SCALE 4:1

SHEET 2 OF 2

REV B

4805 (3/11)