

DE5LC20U

200V 5A


FEATURES

- SMT
- Low noise
- trr35ns

APPLICATION

- Switching power supply
- DC/DC converter
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS



RATINGS


● Absolute Maximum Ratings (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		200	V
Average Rectified Forward Current	Io	50Hz sine wave, R-load, Rating for each diode Io/2, Tc=81°C	5	A
		50Hz sine wave, R-load, Io/2, On alumina substrate Ta=25°C	2.6	
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	50	A


● Electrical Characteristics (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.5A, Pulse measurement, Rating of per diode	Max.0.98	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max.10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A, Rating of per diode	Max.35	ns
Thermal Resistance	θjc	junction to case	Max.12	°C/W
	θja	junction to ambient	Max.55	


DE5LC20U Forward Voltage



DE5LC20U Forward Power Dissipation




$T_j = T_{jmax}$




DE5LC20U

Derating Curve




$$V_R = V_{RM}$$




DE5LC20U


Derating Curve



$$V_R = V_{RM}$$



DE5LC20U Peak Surge Forward Capability



DE5LC20U Junction Capacitance

