





LOC	DIST			REVISIONS				
GP	00	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
					J	REV PER EC QUID-0275-00	03JAN02	JR



1. CONNECTOR MATES WITH ANY 9 POS. PLUG IN AMPLIMITE SERIES & COMPLIES WITH AMP SPEC. 108-40,005 WHERE APPLICABLE.
2. FLAME RETARDANT 94V-0 RATED THERMOPLASTIC; COLOR: BLACK.
3. STEEL PER ASTM A109.
4. PHOS. BRONZE PER QQ-B-750.
5. TIN PLATING PER MIL-T-10727, GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290.
6. TIN PLATED.
7. GOLD FLASH FOR A LENGTH OF .100 MINIMUM FROM MATING END, .000100 MINIMUM TIN-LEAD ON OPPOSITE END, BOTH OVER .000050 MINIMUM NICKEL.
8. .000030 MINIMUM GOLD FOR A LENGTH OF .100 MINIMUM FROM MATING END, .000100 MINIMUM TIN-LEAD ON OPPOSITE END, BOTH OVER .000050 MINIMUM NICKEL.
9. SCREWS ARE FOR -1 & -2.



OBSOLETE	TUBES		745112-4
OBSOLETE	TRAYS		745112-3
	TRAYS		745112-2
OBSOLETE	TRAYS		745112-1
	PACKAGING TYPE	CONTACT FINISH	PART NUMBER



P.C. BOARD MOUNTING DIMENSIONS

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON :

MATERIAL
MOLDED PARTS: $\triangle 2$
SHELLS & BRACKETS: $\triangle 3$

Diagram of a race track with a finish line and a triangle labeled 5.

CONTACTS: SEE TABLE

DR	12-29-83
	J. GERACE

CHK	12-29-8
	J. GERAC

APPD 3-15-84
P. SWEIGARD

APPD	3-15-84
	J. ASSINI

PRODUCT SPEC	
--------------	--

APPLICATION SPEC

1

WEIGHT

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME RECEPTACLE ASSEMBLY, SIZE 1,
9 POS., RIGHT ANGLE,
.545 SERIES, .025 SQ. POSTS,
AMBI-MITE™ HDR

SIZE	CAGE CODE	DRAWING NO.
C	00779	C-745112
SCALE	NTS	SHEET 1 OF 1

CUSTOMER DRAWING