

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 1/23	
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	04	02	04	C


EGSTON

Switch Mode Power Supply

Product Name: P2xFSW3 6W

Standard Programme

Input:	90 - 264 V AC
Output :	3,0V – 24V max. 6W max. 1,2A
Type:	P2xFSW3 6W



CONFIDENTIAL

This document contains proprietary information originated and/or owned by EGSTON GmbH. This information shall not be duplicated, used or disclosed in whole, or in part, to any other party or used for any other purpose without the prior consent of EGSTON GmbH.

Copyright © 2004 EGSTON GmbH.
A-3730 Eggenburg, Grafenberger Strasse 37
All Rights Reserved.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 2/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

Table of Contents

1	Revision History	3
1.1	Evolution	3
2	Scope	3
3	Technical Specification Sheet	4
3.1	Input Specification	4
3.2	Safety and Environmental Conditions	4
3.3	Output Specification	5
3.3.1	Output template	6
3.3.2	Output Ripple Voltage	7
3.4	Mechanical Parameters	9
3.4.1	Housing dimension	9
3.4.2	Housing Material	11
3.5	Cable And Connector	12
3.6	Marking on the housing	12
3.6.1	Plug In Devices	12
3.6.2	Desktop Devices	13
4	EMC	14
4.1	Emission with representative 12V device:	14
4.2	Immunity To Flicker	16
4.3	Immunity to Fast Transients (Burst)	16
4.4	Immunity to Radiated Electromagnetic Field	16
4.5	Immunity to Electrostatic Discharge	16
4.6	Surge Capability	16
4.7	Immunity to conducted disturbances	16
4.8	Immunity to voltage dips, short interruptions and voltage variations	16
5	Reliability	17
5.1	MTBF	17
5.2	Maintainability	17
6	Safety	18
6.1	Dielectric Strength	18
6.2	Over-current Protection	18
6.3	Single Component Failure	18
6.4	Short Circuit	18
7	Approvals and test standards	19
7.1	Test Standards	19
7.2	Approvals	19
7.2.1	EU/UK devices	19
7.2.2	US devices	20
7.2.3	Desktop Devices	20
8	Ordering Information	21
9	Packaging and weight	22
10	Specials Features:	23
10.1	Output voltage tolerance 1%	23
10.2	Visual operation Display (green LED)	23
10.3	Current regulation	23
10.4	Pluggable secondary cable	23
10.5	Customer specific secondary Plug	23
10.6	Australian Primary plug	23
10.7	Print module	23

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 3/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

1 REVISION HISTORY

1.1 Evolution

Edition	Date	Responsible	Reason of change
A	28.05.2003	Obritzhauser	First edition
B	29.07.2003	Obritzhauser	EMV Standards Revised
C	04.02.2004	Obritzhauser	Voltage Range Extended

2 SCOPE

This document describes a switch mode power supply unit (AC/DC) with fixed output voltage.

The unit is designed as a plug in power supply or an Desk Top Module.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 4/23			
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			04	02	04	C

3 TECHNICAL SPECIFICATION SHEET

3.1 Input Specification

Parameter	Key	Min	Typ.	Max	Unit	Test Cond.
Input Voltage	U_{IN}	90		264	V	AC
Input Current	I_{IN}	3	145	175	mA	
Input Frequency	f_{IN}	47		63	Hz	
Efficiency	η	65		80	%	at full load
Switching Frequency	f_{sw}		40		kHz	
Stand-by power	P_{stb}		400		mW	Without load

Input Voltage

If the input voltage is out of operating range, the power supply does not meet the full specification. Above the specified upper limit of the input voltage the unit can get damaged. Below the specified lower limit of the input voltage the unit does not meet the specification.

Efficiency Under Load

The efficiency is defined as the ratio between the output power and input power.

3.2 Safety and Environmental Conditions

Sec	Parameter	Key	Min	Typ.	Max	Unit	Test Cond.
	Dielectric Strength		4,24			kV _{DC}	
	Operating Temperature		-5		40	°C	
			23		104	°F	
	Storage Temperature		-30	25	80	°C	
			-22	77	176	°F	
	Humidity				95	%	

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 5/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C


3.3 Output Specification

Parameter	Key	Min	Typ.	Max	Unit	Test Cond.	Available on request
Output Voltage	U_2	3		24	V	0 – 1,2 A	
Output voltage tolerance	T_{U2}			3	%	at PCB	1% Cable compensation
Output Current	$I_{2 \text{ Nominal}}$	1,2			A		Current regulation
Max. Overload current	$I_{2 \text{ Overload}}$		250 150		% of $I_{2 \text{ Nominal}}$	$U_{IN} = 264V$ $U_{IN} = 90V$	
Output Power	P_2		6		W		
Ripple Voltage	$U_{2,rms}$			50 50	mV _{rms}	$U_{IN} = 264V$ $U_{IN} = 90V$	

The unit is not long time overload proof. If the unit is powered longer than 1 min in overload conditions (current range between $I_{2 \text{ Nominal}}$ and $I_{2 \text{ Overload}}$), the device can be damaged.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 6/23			
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			04	02	04	C

3.3.1 Output template



Specified operating area:

At an output current from 0A to $I_{2\text{ Nominal}}$ the unit fulfills all specified data.

Overload area:

At an output current from $I_{2\text{ Nominal}}$ to $I_{2\text{ Overload}}$ the power supply delivers the specified output voltage U_2 .

The unit is not long time overload proof. If the unit is powered longer than 1 min in overload conditions, the device can be damaged.

Trickle mode area:


If the power demand would be higher than $I_{2\text{ Overload}}$ or the power supply works in short circuit the output voltage and current can not be defined (this parameters are not stable). The wattage of the SMPS is de-rated. In this mode the unit can not be damaged. After removing this conditions the unit fulfills the specification.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 7/23
	Document prepared and responsible for			
	M. Obritzhauser		Standard Programme	
	Responsible for technical data		Day	Month
	M. Obritzhauser		04	02
			Year	Revision
			04	C


3.3.2 Output Ripple Voltage

The output ripple voltage is measured with an oscilloscope 20Mhz band limited at a representative 12V sample.

3.3.2.1 Measurement at 230V input voltage and 0,5A load




Ripple Voltage at switching frequency measured at a temperature of +25°C




Ripple Voltage at mains frequency measured at a temperature of +25°C

	PRODUCT SPECIFICATION P2xFSW3 6W				Page 8/23
	Document prepared and responsible for				
	M. Obritzhauser				Standard Programme
	Responsible for technical data				
	M. Obritzhauser	Day	Month	Year	Revision
		04	02	04	C

3.3.2.2 Measurement at 120V input voltage and 0,5A load



Ripple Voltage at switching frequency measured at a temperature of +25°C




Ripple Voltage at mains frequency measured at a temperature of +25°C

	PRODUCT SPECIFICATION P2xFSW3 6W				Page 9/23		
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			04	02	04	C

3.4 Mechanical Parameters


3.4.1 Housing dimension

3.4.1.1 Euro housing




	PRODUCT SPECIFICATION P2xFSW3 6W			Page 10/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

3.4.1.2 US Housing




3.4.1.3 UK Housing




	PRODUCT SPECIFICATION P2xFSW3 6W			Page 11/23	
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	04	02	04	C

3.4.1.4 Desk Top Housing

With IEC 320 C14 Primary Plug



With IEC 320 C8 primary Plug



3.4.2 Housing Material

	6W UK,EURO,US	12W UK,EURO,US	24W UK,EURO,US	DESKTOP
Material	PA6,V0 Technyl C50H2	PA6,V0 Technyl C50H2	PA6,V0 Technyl C50H2	PA6,V0 Technyl C50H2
Flammability rate	V0	V0	V0	V0

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 12/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

3.5 Cable And Connector

According customer's requirements.

3.6 Marking on the housing

3.6.1 Plug In Devices

3.6.1.1 EU/UK devices

Laser marking
Product name
Input parameters
Output parameters
Product code
Safety Instructions

 Conformity Mark with the EU low voltage directive and EMC directive

 ENEC Mark

 GS Mark

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 13/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

3.6.1.2 US devices

Laser marking
Product name
Input parameters
Output parameters
Product code
Safety Instructions



Conformity Mark with the EU low voltage directive and EMC directive



GS Mark



UL Mark for Canada and the United States

3.6.2 Desktop Devices

Laser marking
Product name
Input parameters
Output parameters
Product code
Safety Instructions



Conformity Mark with the EU low voltage directive and EMC directive



ENEC Mark



GS Mark



UL Mark for Canada and the United States

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 14/23	
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	04	02	04	C



4 EMC

The units meet the following EMC requirements:

4.1 Emission with representative 12V device:

Test passed according to EN55022 Class B.


Primary: 230V AC, Secondary: 12V / 500mA , Temperature: 25°C, Load connected to ground, Peak and Average Measurement.



	PRODUCT SPECIFICATION P2xFSW3 6W			Page 15/23
	Document prepared and responsible for			
	M. Obritzhauser			Standard Programme
	Responsible for technical data			Day Month Year Revision
	M. Obritzhauser			04 02 04 C

Test passed according to FCC15 Class B.

Primary: 120V AC, Secondary: 12V / 500mA , Temperature: 25°C, Load connected to ground, Peak Measurement



	PRODUCT SPECIFICATION P2xFSW3 6W			Page 16/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

4.2 Immunity To Flicker

Test according to EN 61000-3-2

4.3 Immunity to Fast Transients (Burst)

Test according to EN61000-4-4

Input Line: 2.0kV – 5/50 ns – 5.0 kHz

Output Line: 2.0kV – 5/50 ns – 5.0 kHz

4.4 Immunity to Radiated Electromagnetic Field

Test according to EN 61000-4-3

Test characteristic: 80 – 1000 MHz; 80% AM (1kHz), 3V/m

4.5 Immunity to Electrostatic Discharge

Test according to EN 61000-4-2

Test characteristic: Contact discharge 6kV

Air discharge 8kV

4.6 Surge Capability

Test according to EN61000-4-5

Test characteristic: line to line: 1kV Surge

line to earth: 2kV Surge

4.7 Immunity to conducted disturbances

Test according to EN 61000-4-6

Test characteristic: 150kHz – 80 MHz; 80% AM (1kHz), 3V

4.8 Immunity to voltage dips, short interruptions and voltage variations

Test according to EN 61000-4-11

Test criterion C

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 17/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

5 RELIABILITY

5.1 MTBF

at 240V input voltage $\geq 1.900.000$ hours

at 100V input voltage $\geq 2.400.000$ hours

MTBF calculation according SN 29500 at 40°C ambient temperature

5.2 Maintainability

The power supply is not to be repaired.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 18/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

6 SAFETY

The units pass the following tests:

6.1 Dielectric Strength

The input isolation test voltage is 3kV 50/60 Hz, sinusoidal waveform. Test duration is 2 seconds for 100% test, 1 minute 4,24KV DC or lot-test..

6.2 Over-current Protection

The unit is not long time over-current proof. If the unit is powered longer than 1 min in overload conditions, the device can be damaged.

6.3 Single Component Failure

A single component failure does not cause any damage to persons or ambient (fire, explosions, etc).

6.4 Short Circuit

The power supply is designed with a short circuit protection. A shortened output does not cause any damage to persons or ambient (fire, explosions, etc.) After removing this conditions the unit fulfills the specification.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 19/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

7 APPROVALS AND TEST STANDARDS

7.1 Test Standards

EN 60 950
 UL 1310
 EN 61000-6-1
 EN 55022
 EN 55011
 EN 55014-1
 EN 61204-3

7.2 Approvals

7.2.1 EU/UK devices



Conformity with the EU low voltage directive and EMC directive



ENEC



GS

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 20/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

7.2.2 US devices

 Conformity with the EU low voltage directive and EMC directive



GS



UL for Canada and the United States

7.2.3 Desktop Devices

 Conformity with the EU low voltage directive and EMC directive



ENEC



GS



UL for Canada and the United States

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 21/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

8 ORDERING INFORMATION

	POWER CLASS	6 Watt
P	SUPPLY TYPE	P = New Generation Power Supply
2	OPERATION TEMP. RANGE	2 = -5°C to +40°C
E	PRIMARY CONNECTOR	E = Euro plug U = US/Japan/Canada Plug G = United Kingdom Plug D = Desktop Module
F	CABLE CONNECTION	F = Fixed
S	APPLICATION	S = Standard M = Medical H = Household
W	WIDE INPUT RANGE	W = 90V-264V
3	OUTPUT STABILITY	3 = 3%
6W	HOUSING DIMENSION	6W
6V	OUTPUT VOLTAGE	3V-24V
1A	OUTPUT CURRENT	1200mA max.

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 22/23			
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			04	02	04	C

9 PACKAGING AND WEIGHT

Cable with connector 5.5/2.1											38 g		
Instruction Manual											3.6 g		
Euro pallet empty (wooden):											21 kg		
SINGLE PACKAGING			PS 1.5m cable+connector 5.5/2.1	Single carton empty	Single carton full	Packing case empty	Packing unit	Packing case full	Cartons per pallet	Euro pallet full	Single carton	Packing case	Euro pallet
P2	EU	6W	120	13	137	180	50	7.1	27	213	126x68.5x43.5	351x260x226	1200x800x
P2	US	6W	120	13	137	180	50	7.1	27	213	126x68.5x43.5	351x260x226	1200x800x
P2	Uk	6W	120	16	140	180	50	7.2	18	151	136x76x50.5	388x280x260.5	1200x800x
Unit			g	g	g	g	Pcs.	kg	Pcs.	kg	mm	mm	mm

	PRODUCT SPECIFICATION P2xFSW3 6W			Page 23/23		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		04	02	04	C

10 SPECIALS FEATURES:

Following Specials can be offered on request

10.1 Output voltage tolerance 1%

The output voltage can be adjusted with a tolerance of $\pm 1\%$.

10.2 Visual operation Display (green LED)

When the green led is shining the output voltage is delivered.

10.3 Current regulation

The secondary voltage will be reduced when the selected output current is reached.

The max. Current which can be selected is 80% of $I_{2 \text{ Nominal}}$.

The current regulation can be delivered at the secondary voltage range from 5 to 24V.

10.4 Pluggable secondary cable

Only available at Egston Standard - Plug In Powersupplies.

10.5 Customer specific secondary Plug

10.6 Australian Primary plug

10.7 Print module

The power supply is built in a housing which can be soldered on to a PCB.