



DataTraveler Vault — Privacy

Protect data with 256-bit AES encryption and 100% privacy.

Kingston's DataTraveler® Vault — Privacy Edition USB Flash drive is designed for organizations that require a secure way to store and transfer portable data. One hundred percent of the stored data is secured by hardware-based, 256-bit AES encryption to guard sensitive information in case the drive is lost or stolen. It's waterproof¹ and its durable, aluminum casing provides added protection.

Assembled in the U.S., DataTraveler Vault — Privacy Edition fully supports Mac OS X and is backed by a five-year warranty, free technical support and legendary Kingston® reliability.



Assembled
in the USA



Features/specs on reverse >>

DataTraveler Vault – Privacy

FEATURES/BENEFITS

- > **Enterprise-Grade Security** — 100-percent of stored data is protected by hardware-based, 256-bit Advanced Encryption Standard (AES) in Cipher Block Chaining (CBC) mode
- > **Fast**² — data transfer rates of up to 24MB/s read and up to 10MB/s write
- > **Read-Only Access Mode**³ — when selected, access files in Read-only Mode to avoid potential Malware risks
- > **Secure** — drive locks down and reformats after 10 intrusion attempts
- > **Enforced password protection** — complex password is user set with minimum characteristics to prevent unauthorized access
- > **Fully Supports Macintosh OS X**
- > **Easy to use** — no admin rights or application installation required
- > **Customizable**⁴ — preload content, password length, maximum number of password attempts
- > **Co-Logo available**⁴
- > **Compatibility** — designed to USB 2.0 specifications
- > **Guaranteed** — five-year warranty with free technical support
- > **Durable** — aluminum casing
- > **Waterproof**¹ — protects against water damage
- > **TAA Compliant**
- > **Assembled in the U.S.**

SPECIFICATIONS

- > **Dimensions** 3.06" x 0.9" x 0.47" (77.9mm x 22mm x 12.05mm)
- > **Capacities**⁵ 2GB, 4GB, 8GB, 16GB, 32GB, 64GB
- > **Operating Temperature** 32°F to 140°F (0°C to 60°C)
- > **Storage Temperature** -4°F to 185°F (-20°C to 85°C)
- > **Minimum System Requirements:**
 - USB 2.0 compliant and 1.1 compatible
 - Two (2) free drive letters required for use⁶



1 Up to 4 ft.; conforms to IEC 60529 IPX8. Product must be clean and dry before use.

2 For 2GB capacity, data transfer rates of up to 17MB/s read and 9MB/s write. Speed may vary due to host hardware, software and usage.

3 Read-Only feature is available in the Windows and Mac interfaces only.

4 Minimum quantity required. Performed at the factory.

5 Please note: Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash Guide at kingston.com/pdfs/FlashMemGuide.pdf.

6 First free drive letters after physical devices such as system partition, optical drives, etc.

7 Certain distributions of Linux will require super-user (root) privileges in order to execute the DataTraveler Vault — Privacy commands properly in the terminal application window.

THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2012 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-185.2US



COMPATIBILITY TABLE

Windows® 7	✓
Windows Vista® (SP1,SP2)	✓
Windows XP (SP2,SP3)	✓
Mac OS X(10.5.x - 10.6.x)	✓
Linux v2.6 kernel ⁷	✓

KINGSTON PART NUMBERS

DTVP/2GB
DTVP/4GB
DTVP/8GB
DTVP/16GB
DTVP/32GB
DTVP/64GB

