

ES51F5G15AN-28.332M

[Click part number to visit Part Number Details page](#)

REGULATORY COMPLIANCE (Data Sheet downloaded on Apr 27, 2016)



ITEM DESCRIPTION

Temperature Compensated Quartz Crystal Clock Oscillators TCXO Clipped Sinewave 5.0Vdc 14-Pin DIP Metal Thru-Hole 28.332MHz $\pm 1.0\text{ppm}$ Maximum $\pm 1.5\text{ppm}$ Maximum 0°C to $+50^{\circ}\text{C}$

ELECTRICAL SPECIFICATIONS

Nominal Frequency	28.332MHz
Initial Tolerance	$\pm 1.0\text{ppm}$ Maximum (Measured at Nominal Vdd and Vc)
Frequency Stability	$\pm 1.5\text{ppm}$ Maximum
Frequency Stability vs. Input Voltage	$\pm 0.3\text{ppm}$ Maximum (Vdd $\pm 5\%$)
Frequency Stability vs. Load	$\pm 0.2\text{ppm}$ Maximum ($\pm 10\%$)
Frequency Stability vs. Aging	$\pm 1\text{ppm}/\text{Year}$ Maximum (at 25°C)
Operating Temperature Range	0°C to $+50^{\circ}\text{C}$
Supply Voltage	5.0Vdc $\pm 5\%$
Input Current	10mA Maximum (Measured at Steady State at 25°C)
Output Voltage	1.0Vp-p Minimum Clipped Sinewave
Load Drive Capability	10kOhms//10pF
Output Logic Type	Clipped Sinewave
Control Voltage	None (No Connect on Pin 1)
Internal Trim	$\pm 3\text{ppm}$ Minimum (at 25°C , Top Access)
Input Impedance	10kOhms Typical
Phase Noise	-70dBc/Hz at 10Hz Offset, -100dBc/Hz at 100Hz Offset, -130dBc/Hz at 1kHz Offset, -140dBc/Hz at 10kHz Offset, -145dBc/Hz at 100kHz Offset (Typical Values at 19.440MHz)
Storage Temperature Range	-55°C to $+125^{\circ}\text{C}$


ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

Fine Leak Test	MIL-STD-883, Method 1014 Condition A (Internal Crystal Only)
Gross Leak Test	MIL-STD-883, Method 1014 Condition C (Internal Crystal Only)
Lead Integrity	MIL-STD-883, Method 2004
Mechanical Shock	MIL-STD-202, Method 213 Condition C
Resistance to Soldering Heat	MIL-STD-202, Method 210
Resistance to Solvents	MIL-STD-202, Method 215
Solderability	MIL-STD-883, Method 2003
Temperature Cycling	MIL-STD-883, Method 1010
Vibration	MIL-STD-883, Method 2007 Condition A

ES51F5G15AN-28.332M

[Click part number to visit Part Number Details page](#)

MECHANICAL DIMENSIONS (all dimensions in millimeters)





LINE	MARKING
1	ECLIPTEK
2	28.332M
3	XXYYZZ XX=Ecliptek Manufacturing Code Y=Last Digit of the Year ZZ=Week of the Year

ES51F5G15AN-28.332M [Click part number to visit Part Number Details page](#)



OUTPUT WAVEFORM



ES51F5G15AN-28.332M
[Click part number to visit Part Number Details page](#)
Test Circuit for No Connect Option

Note 1: An external 0.1µF low frequency tantalum bypass capacitor in parallel with a 0.01µF high frequency ceramic bypass capacitor close to the package ground and V_{DD} pin is required.


Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.

Note 3: Capacitance value C_L includes sum of all probe and fixture capacitance.

ES51F5G15AN-28.332M [Click part number to visit Part Number Details page](#)



Recommended Solder Reflow Methods



Low Temperature Solder Bath (Wave Solder)

TS MAX to TL (Ramp-up Rate)		5°C/Second Maximum
Preheat		
- Temperature Minimum (TS MIN)	N/A	
- Temperature Typical (TS TYP)	150°C	
- Temperature Maximum (TS MAX)	N/A	
- Time (ts MIN)	30 - 60 Seconds	
Ramp-up Rate (TL to TP)		5°C/Second Maximum
Time Maintained Above:		
- Temperature (TL)	150°C	
- Time (tL)	200 Seconds Maximum	
Peak Temperature (TP)		245°C Maximum
Target Peak Temperature (TP Target)		245°C Maximum 1 Time / 235°C Maximum 2 Times
Time within 5°C of actual peak (tp)		5 Seconds Maximum 1 Time / 15 Seconds Maximum 2 Times
Ramp-down Rate		5°C/Second Maximum
Time 25°C to Peak Temperature (t)		N/A
Moisture Sensitivity Level		Level 1

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum.

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum.