



# GENERAL PURPOSE – SINGLE POLE

# E Series



## Features

- Choice of 5 contact ratings
- Long life coil spring, snap action mechanism
- Agency approved extended life versions available
- High Temperature 200°C versions available
- RoHS Compliant

## Electrical Ratings and Operating Life

| According to UL1054 |                                                                 |                                   |
|---------------------|-----------------------------------------------------------------|-----------------------------------|
| Switch Series       | Nominal Load                                                    | Operation cycles (Min operations) |
| G13                 | 0.1A 125VAC, 0.1A 30VDC                                         | 6000*                             |
| E13                 | 15A, 125/250VAC; 3/4HP 125VAC<br>1 ½ hp 250VAC; 2A 48VDC        | 6000*                             |
| E14                 | 25A 125/250VAC; 1HP 125VAC<br>2HP 250VAC; 2A 48VDC              | 6000                              |
| E30                 | 30.1A 125/250VAC; 1HP 125VAC<br>2HP 250VAC (UL Only)            | 6000                              |
| E29                 | 30.1A 125/250/277 VAC<br>UL Approved Only – Resistive Load Only | 6000                              |

- Extended life 105°C UL versions available. Contact factory for more information. Special part number required.

| Technical Specifications |                                                                                                 | Material Specifications |                                                                                   |
|--------------------------|-------------------------------------------------------------------------------------------------|-------------------------|-----------------------------------------------------------------------------------|
| Temperature Ratings:     | -40°C to 105°C (G13, E13, E14)<br>-40°C to 85°C (E29)<br>150°C & 200°C optional (G13, E13, E14) | Case:                   | General Purpose Phenolic                                                          |
|                          |                                                                                                 | Actuator button:        | Thermoplastic Nylon                                                               |
|                          |                                                                                                 | Common Terminal:        | Brass: G13 and E13<br>Silver Plated Brass: E14<br>Silver Plated Copper (E29, E30) |
| Flammability Rating:     | UL94HB                                                                                          | Terminals:              | Brass (G13, E13)<br>Copper (E14, E29, E30)                                        |
| Terminals:               | 0.250" x 0.032" (6.35mm x 0.81mm)                                                               | Moving Blade:           | Brass (G13, E13)<br>Silver Plated Beryllium Copper (E14, E29, E30)                |
|                          |                                                                                                 | Spring:                 | Stainless Steel                                                                   |
| CSA File Number          | 16503                                                                                           | Auxiliary Actuator:     | Cold-Rolled Stainless Steel (Nickel Plated)                                       |
| UL File Number:          | E23301                                                                                          | Contacts:               | Silver-CdO: E13, E14, E29, E30<br>Gold Crosspoint: G13                            |

Specifications subject to change





(G13, E13,  
E14 @ T200)




## GENERAL PURPOSE – SINGLE POLE

# E Series

Dimensions - inches



-00J (White plastic button)



-00M (Metal cap over button)

### Commonly Stocked Distributor Items / Preferred Part Numbers


| Item Number | EN Rating | UL Rating                                             | Maximum Pretravel inches (mm) | Operating Point inches (mm)      | Minimum Overtravel inches (mm) | Max. Movement Differential inches (mm) | Maximum Operating Force (grams) | Actuation Length inches (mm) |
|-------------|-----------|-------------------------------------------------------|-------------------------------|----------------------------------|--------------------------------|----------------------------------------|---------------------------------|------------------------------|
| 0E1300E0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.050 (1.27)                  | 0.285 +/- 0.020 (7.24 +/- 0.51)  | 0.100 (2.54)                   | 0.015 (0.38)                           | 425                             | N/A                          |
| 0E1300H0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.250 (6.35)                  | 0.312 +/- .062 (7.93 +/- 1.57)   | 0.187 (4.75)                   | 0.093 (2.36)                           | 100                             | 1.50 (38.10)                 |
| 0E1300J0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.050 (1.27)                  | 0.870 +/- .030 (21.84 +/- 0.76)  | 0.108 (2.74)                   | 0.015 (0.38)                           | 425                             | N/A                          |
| 0E1300K0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.250 (6.35)                  | 0.718 +/- 0.062 (18.24 +/- 1.57) | 0.718 (4.75)                   | 0.093 (2.36)                           | 100                             | 1.39 (35.31)                 |
| 0E1300M0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.050 (1.27)                  | 0.812 +/- 0.030 (20.63 +/- 0.76) | 0.218 (5.54)                   | 0.015 (0.38)                           | 425                             | N/A                          |
| 0E1301E0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.050 (1.27)                  | 0.285 +/- 0.020 (7.24 +/- 0.51)  | 0.100 (2.54)                   | 0.015 (0.38)                           | 425                             | N/A                          |
| 0E1301H0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.250 (6.35)                  | 0.312 +/- .062 (7.93 +/- 1.57)   | 0.187 (4.75)                   | 0.093 (2.36)                           | 100                             | 1.50 (38.10)                 |
| 0E1350H0    | N/A       | 15A, 125/250VAC; 3/4HP 125VAC 1 1/2HP 250VAC 2A 48VDC | 0.343 (8.71)                  | 0.281 +/- 0.062 (7.14 +/- 1.57)  | 0.187 (4.75)                   | 0.140 (3.56)                           | 65                              | 1.75 (44.45)                 |
| 0E1400A0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.100 (2.54)                  | 0.248 +/- 0.026 (6.30 +/- 0.66)  | 0.050 (1.27)                   | 0.015 (0.38)                           | 850                             | N/A                          |
| 0E1400H0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.312 (7.93)                  | 0.468 +/- 0.062 (11.84 +/- 1.57) | 0.105 (2.67)                   | 0.050 (1.27)                           | 100                             | 0.821 (20.85)                |
| 0E1400K0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.348 (8.84)                  | 0.860 +/- 0.062 (21.84 +/- 1.57) | 0.130 (3.30)                   | 0.045 (1.14)                           | 285                             | 0.688 (17.47)                |
| 0E1400M0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.100 (2.54)                  | 0.775 +/- 0.25 (19.69 +/- 6.35)  | 0.168 (4.27)                   | 0.015 (0.38)                           | 850                             | N/A                          |
| 0E1401M0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.100 (2.54)                  | 0.775 +/- 0.25 (19.69 +/- 6.35)  | 0.168 (4.27)                   | 0.015 (0.38)                           | 850                             | N/A                          |
| 0E1450H0    | N/A       | 25A 125/250VAC 1HP 125VAC 2HP 250VAC; 2A 48VDC        | 0.525 (13.34)                 | .437 +/- 0.062 (11.10 +/- 1.57)  | 0.218 (5.54)                   | 0.080 (2.03)                           | 170                             | 1.071 (27.20)                |
| 0G1300M0    | N/A       | 0.1A 125VAC, 0.1A 30VDC                               | 0.050 (1.27)                  | 0.812 +/- 0.030 (20.63 +/- 0.76) | 0.218 (5.54)                   | 0.015 (0.38)                           | 425                             | N/A                          |
| 0G1350H0    | N/A       | 0.1A 125VAC, 0.1A 30VDC                               | 0.343 (8.71)                  | 0.281 +/- 0.062 (7.14 +/- 1.57)  | 0.187 (4.75)                   | 0.140 (3.56)                           | 65                              | 1.75 (44.45)                 |




## GENERAL PURPOSE – SINGLE POLE

# E Series

### Actuator Details



Flat Actuator Version



Roller Actuator Version

### “J” and “M” Type Optional Hardware

|                               |           |
|-------------------------------|-----------|
| Brass Hex Nut                 | 0012-0023 |
| Brass Hex Nut (Nickel Plated) | 0012-0028 |

### Mounting

Recommended mounting screw: #6-32 round head. Recommended torque on screw: 6 inch-lbs. max.

Recommended torque on ferrule: 20 inch lbs. max.

### Ordering Information

|                                   |                                        |                  |
|-----------------------------------|----------------------------------------|------------------|
| Select the desired contact rating | Combine with the button/actuator style | Full part number |
| <b>E13</b>                        | <b>50H</b>                             | <b>E13-50H</b>   |

#### For single throw versions:

|                                   |                               |                                     |                                      |
|-----------------------------------|-------------------------------|-------------------------------------|--------------------------------------|
| Select the desired contact rating | Combine with the button style | SPST – NO                           | SPST - NC                            |
| <b>E13</b>                        | <b>50H</b>                    | <b>E13-51H</b><br>(Add 1 to suffix) | <b>0E13-52H</b><br>(Add 2 to suffix) |

### Contact

Call, fax or visit our Website for more information.

**ZF Electronics Corporation**  
11200 88th Avenue  
Pleasant Prairie, WI 53158

Phone: 262.942.6500  
Web: [www.cherrycorp.com](http://www.cherrycorp.com)  
Email: [cep\\_sales@zf.com](mailto:cep_sales@zf.com)  
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2007 ZF Electronics Corporation

Last Updated: 031411

