




LOC	DIST	REVISIONS					
AD	39	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-11-004820	11MAR11	RK	HMR



1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.00254–0.00508 [.000100–.000200] BRIGHT TIN–LEAD OVER 0.00127 [.000050] NICKEL ENTIRE POST.
6. FINISH: 0.00254–0.00508 [.000100–.000200] MATTE TIN OVER 0.00127 [.000050] NICKEL ENTIRE POST.

6	101.19 [3.984]	99.06 [3.900]	39	40	9-146468-0
6	98.65 [3.884]	96.52 [3.800]	38	39	8-146468-9
6	96.11 [3.784]	93.98 [3.700]	37	38	8-146468-8
6	93.57 [3.684]	91.44 [3.600]	36	37	8-146468-7
6	91.03 [3.584]	88.90 [3.500]	35	36	8-146468-6
6	88.49 [3.484]	86.36 [3.400]	34	35	8-146468-5
6	85.95 [3.384]	83.82 [3.300]	33	34	8-146468-4
6	83.41 [3.284]	81.28 [3.200]	32	33	8-146468-3
6	80.87 [3.184]	78.74 [3.100]	31	32	8-146468-2
6	78.33 [3.084]	76.20 [3.000]	30	31	8-146468-1
6	75.79 [2.984]	73.66 [2.900]	29	30	8-146468-0
6	73.25 [2.884]	71.12 [2.800]	28	29	7-146468-9
6	70.71 [2.784]	68.58 [2.700]	27	28	7-146468-8
6	68.17 [2.684]	66.04 [2.600]	26	27	7-146468-7
6	65.63 [2.584]	63.50 [2.500]	25	26	7-146468-6
6	63.09 [2.484]	60.96 [2.400]	24	25	7-146468-5
6	60.55 [2.384]	58.42 [2.300]	23	24	7-146468-4
6	58.01 [2.284]	55.88 [2.200]	22	23	7-146468-3
6	55.47 [2.184]	53.34 [2.100]	21	22	7-146468-2
6	52.93 [2.084]	50.80 [2.000]	20	21	7-146468-1
6	50.39 [1.984]	48.26 [1.900]	19	20	7-146468-0
6	47.85 [1.884]	45.72 [1.800]	18	19	6-146468-9
6	45.31 [1.784]	43.18 [1.700]	17	18	6-146468-8
6	42.77 [1.684]	40.64 [1.600]	16	17	6-146468-7
6	40.23 [1.584]	38.10 [1.500]	15	16	6-146468-6
6	37.69 [1.484]	35.56 [1.400]	14	15	6-146468-5
6	35.15 [1.384]	33.02 [1.300]	13	14	6-146468-4
6	32.61 [1.284]	30.48 [1.200]	12	13	6-146468-3
6	30.07 [1.184]	27.94 [1.100]	11	12	6-146468-2
6	27.53 [1.084]	25.40 [1.000]	10	11	6-146468-1
6	24.99 [.984]	22.86 [.900]	9	10	6-146468-0
6	22.45 [.884]	20.32 [.800]	8	9	5-146468-9
6	19.91 [.784]	17.78 [.700]	7	8	5-146468-8
6	17.37 [.684]	15.24 [.600]	6	7	5-146468-7
6	14.83 [.584]	12.70 [.500]	5	6	5-146468-6
6	12.29 [.484]	10.16 [.400]	4	5	5-146468-5
6	9.75 [.384]	7.62 [.300]	3	4	5-146468-4
6	7.21 [.284]	5.08 [.200]	2	3	5-146468-3
6	4.67 [.184]	2.54 [.100]	1	2	5-146468-2
6	2.13 [.084]	-	-	1	5-146468-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

5	101.19 [3.984]	99.06 [3.900]	39	40	4-146468-0
5	98.65 [3.884]	96.52 [3.800]	38	39	3-146468-9
5	96.1 [3.784]	93.98 [3.700]	37	38	3-146468-8
5	93.57 [3.684]	91.44 [3.600]	36	37	3-146468-7
5	91.03 [3.584]	88.90 [3.500]	35	36	3-146468-6
5	88.49 [3.484]	86.36 [3.400]	34	35	3-146468-5
5	85.95 [3.384]	83.82 [3.300]	33	34	3-146468-4
5	83.41 [3.284]	81.28 [3.200]	32	33	3-146468-3
5	80.87 [3.184]	78.74 [3.100]	31	32	3-146468-2
5	78.33 [3.084]	76.20 [3.000]	30	31	3-146468-1
5	75.79 [2.984]	73.66 [2.900]	29	30	3-146468-0
5	73.25 [2.884]	71.12 [2.800]	28	29	2-146468-9
5	70.71 [2.784]	68.58 [2.700]	27	28	2-146468-8
5	68.17 [2.684]	66.04 [2.600]	26	27	2-146468-7
5	65.63 [2.584]	63.50 [2.500]	25	26	2-146468-6
5	63.09 [2.484]	60.96 [2.400]	24	25	2-146468-5
5	60.55 [2.384]	58.42 [2.300]	23	24	2-146468-4
5	58.01 [2.284]	55.88 [2.200]	22	23	2-146468-3
5	55.47 [2.184]	53.34 [2.100]	21	22	2-146468-2
5	52.93 [2.084]	50.80 [2.000]	20	21	2-146468-1
5	50.39 [1.984]	48.26 [1.900]	19	20	2-146468-0
5	47.85 [1.884]	45.72 [1.800]	18	19	1-146468-9
5	45.31 [1.784]	43.18 [1.700]	17	18	1-146468-8
5	42.77 [1.684]	40.64 [1.600]	16	17	1-146468-7
5	40.23 [1.584]	38.10 [1.500]	15	16	1-146468-6
5	37.69 [1.484]	35.56 [1.400]	14	15	1-146468-5
5	35.15 [1.384]	33.02 [1.300]	13	14	1-146468-4
5	32.61 [1.284]	30.48 [1.200]	12	13	1-146468-3
5	30.07 [1.184]	27.94 [1.100]	11	12	1-146468-2
5	27.53 [1.084]	25.40 [1.000]	10	11	1-146468-1
5	24.99 [.984]	22.86 [.900]	9	10	1-146468-0
5	22.45 [.884]	20.32 [.800]	8	9	146468-9
5	19.91 [.784]	17.78 [.700]	7	8	146468-8
5	17.37 [.684]	15.24 [.600]	6	7	146468-7
5	14.83 [.584]	12.70 [.500]	5	6	146468-6
5	12.29 [.484]	10.16 [.400]	4	5	146468-5
5	9.75 [.384]	7.62 [.300]	3	4	146468-4
5	7.21 [.284]	5.08 [.200]	2	3	146468-3
5	4.67 [.184]	2.54 [.100]	1	2	146468-2
5	2.13 [.084]	-	-	1	146468-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. 05-MAR-97 BY: BRANDBERG		 TE Connectivity	
		CHK. G. DUBNICZKI 05-MAR-97			
DIMENSIONS: mm: [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 P.C. ± 1 P.C. ± 2 P.C. ± 0.51[.02] 3 P.C. ± 0.127[.005] 4 P.C. ± 0.0254[.001] ANGLES		PRODUCT SPEC	
		FINISH		APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CASE CODE DRAWING NO. RESTRICTED TO A1 00779 C 146468 —	
SEE TABLE		CUSTOMER DRAWING		SCALE: 4:1 SHEET 1 OF 1 REV. A	