



Search Results

- Evaluate
- FAQ's
 - Product Bulletins
 - PDFCONTOURTY C
- Design a Solution
- Part Drawings
 - PDFContour Ty C ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'CBR3IM7'

Your search criteria matched only one product, shown below

CBR3IM7



- For indoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

	Part Number	CBR3IM7
	RoHS Compliancy Status	Compliant
	Part Description	Contour-Ty® Cable Tie, Parallel-entry, 10.4", Intermediate cross section
	Product Type	Cable Ties
	Material	Nylon 6.6
	Color	Purple
	CSA Certified	Yes
	Mil. Std. Part Number	MS3367-34-7
	UL Listed (File #E56854)	Yes
	UL Recognized (File #E56854)	Yes
	Length (In.)	10.4
	Length (mm)	264
	Width (In.)	.140
	Width (mm)	3.6
	CE Compliant	Yes
	Cross Section	Intermediate
	Head Height (In.)	.250
	Head Height (mm)	6.4
	Head Width (In.)	.262
	Head Width (mm)	6.7
	Locking Style	Locking
	Material Flammability Rating	UL 94V-2
	Max. Bundle Diameter (In.)	3.00
	Max. Bundle Diameter (mm)	76
	Max. Continuous Use Temperature	185°F (85°C)
	Min. Loop Tensile Strength (Lbs.)	40
	Min. Loop Tensile Strength (N)	178
	Pricing Description	Cable Tie, InLine, 10.4"L (264mm), Intermediate, Nylon, Purple
	Thickness (In.)	.052
	Thickness (mm)	1.3
	Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
	Min. Order UOM	PC
	Min. Order Qty.	1000
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.