

Features

- Low Forward Voltage Drop
- Guard Ring Construction for Transient Protection
- Low Reverse Recovery Time
- Low Reverse Capacitance
- **Lead Free Finish, RoHS Compliant (Note 2)**

Mechanical Data

- Case: DO-35
- Case Material: Glass
- Moisture Sensitivity: Level 1 per J-STD-020D
- Leads: Solderable per MIL-STD-202, Method 208
- Terminals: Finish — Matte Tin. Solderable per MIL-STD-202, Method 208 
- Polarity: Cathode Band
- Marking Information: See Page 2
- Ordering Information: See Page 2
- Weight: 0.13 grams (approximate)

Maximum Ratings @T_A = 25°C unless otherwise specified

Characteristic	Symbol	SD101A	SD101B	SD101C	Unit
Peak Repetitive Reverse Voltage	V _{RRM}				
Working Peak Reverse Voltage	V _{RWM}	60	50	40	V
DC Blocking Voltage	V _R				
RMS Reverse Voltage	V _{R(RMS)}	42	35	28	V
Forward Continuous Current (Note 1)	I _{FM}		15		mA
Non-Repetitive Peak Forward Surge Current @ t ≤ 1.0s	I _{FSM}	50			mA
@ t = 10μs		2.0			A

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 1)	P _D	400	mW
Thermal Resistance, Junction to Ambient Air (Note 1)	R _{θJA}	375	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-65 to +175	°C

Electrical Characteristics @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Min	Max	Unit	Test Condition
Maximum Forward Voltage Drop	V _{FM}	—	0.41	V	I _F = 1.0mA
SD101B			0.40		I _F = 1.0mA
SD101C			0.39		I _F = 1.0mA
SD101A			1.00		I _F = 15mA
SD101B			0.95		I _F = 15mA
SD101C			0.90		I _F = 15mA
Maximum Peak Reverse Current	I _{RM}	—	200	nA	V _R = 50V
SD101B					V _R = 40V
SD101C					V _R = 30V
Total Capacitance	C _T	—	2.0	pF	V _R = 0V, f = 1.0MHz
SD101B			2.1		
SD101C			2.2		
Reverse Recovery Time	t _{rr}	—	1.0	ns	I _F = I _R = 5.0mA, I _{rr} = 0.1 x I _R , R _L = 100Ω

- Notes:
1. Valid provided that leads are kept at ambient temperature.
 2. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see *EU Directive 2002/95/EC Annex Notes*.




Fig. 1 Typical Forward Characteristics




Fig. 2 Total Capacitance vs. Reverse Voltage


Ordering Information (Note 3)

Part Number	Case	Packaging
SD101A-A	DO-35	10K/Ammo Pack
SD101A-T	DO-35	10K/Tape & Reel, 13-inch
SD101B-A	DO-35	10K/Ammo Pack
SD101B-T	DO-35	10K/Tape & Reel, 13-inch
SD101C-A	DO-35	10K/Ammo Pack
SD101C-T	DO-35	10K/Tape & Reel, 13-inch

 Notes: 3. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

Marking Information


SD101x= Product Type Marking Code
 (SD101A, SD101B, SD101C)
 X = Manufacturers' Code Marking
 YWW = Date Code Marking
 Y = Last digit of (ex: 2 for 2002)
 WW = Week code 01 to 52

Package Outline Dimensions


DO-35		
Dim	Min	Max
A	25.40	—
B	—	4.00
C	—	0.60
D	—	2.00
All Dimensions in mm		

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.