



# **SAW Components**

## **SAW Duplexer**

LTE Band 17

**Series/type:** B7924

**Ordering code:** B39741B7924P810

**Date:** October 06, 2011

**Version:** 2.0

## SAW Components

B7924

### SAW Duplexer

710.0 / 740.0 MHz

Data sheet




#### Application

- Low-loss SAW duplexer for mobile telephone
- LTE Band 17 systems
- High attenuation
- High Isolation
- Low amplitude ripple
- Usable passband 12 MHz
- Single-ended to balanced transformation in Antenna-Rx path
- Impedance transformation  $50 \Omega$  to  $100 \Omega$  in Antenna-Rx path
- Very small size and low height




#### Features

- Package size  $2.5 * 2.0 * 0.68 \text{ mm}^3$
- RoHS compatible
- Package for **Surface Mount Technology (SMT)**
- Ni, Au-plated terminals
- **Electrostatic Sensitive Device (ESD)**
- **Moisture Sensitivity Level 3**



#### Pin configuration

- 3                    Tx input
- 1, 8               Rx output (balanced)
- 6                    Antenna
- 2, 4, 5, 7, 9      To be grounded



Please read *cautions and warnings and important notes* at the end of this document.

<b>SAW Components</b>	<b>B7924</b>
<b>SAW Duplexer</b>	<b>710.0 / 740.0 MHz</b>

Data sheet



### Characteristics

Temperature range for specification:	$T = -30^{\circ}\text{C}$ to $+85^{\circ}\text{C}$
TX terminating impedance:	$Z_{\text{Tx}} = 50 \Omega$
ANT terminating impedance:	$Z_{\text{Ant}} = 50 \Omega \parallel 10 \text{ nH}$
RX terminating impedance:	$Z_{\text{Rx}} = 100 \Omega$ (balanced)

Characteristics Tx-Antenna		min.	typ. @ 25 °C	max.	
<b>Center frequency</b>	$f_c$		710.0		MHz
<b>Maximum insertion attenuation</b>	$\alpha$				
704.0 ... 716.0 MHz			1.6	2.5	dB
<b>Amplitude ripple (p-p)</b>	$\Delta\alpha$				
704.0 ... 716.0 MHz			0.6	1.6	dB
<b>Error Vector Magnitude</b>					
@ $f_{\text{Carrier}}$ 706.4 ... 712.0 MHz	EVM <sup>1)</sup>		1.4	3.5	%
@ $f_{\text{Carrier}}$ 712.0 ... 713.6 MHz	EVM <sup>1)</sup>		1.3	4.0	%
<b>Input VSWR (Tx port)</b>					
704.0 ... 716.0 MHz			1.5	2.0	
<b>Output VSWR (Ant Port)</b>					
704.0 ... 716.0 MHz			1.5	2.0	

<sup>1)</sup> Error Vector Magnitude (EVM) based on definition in 3GPP TS 25.141

**SAW Components**
**B7924**
**SAW Duplexer**
**710.0 / 740.0 MHz**
**Data sheet**

**Characteristics**

Temperature range for specification:

 $T = -30 \text{ }^{\circ}\text{C} \text{ to } +85 \text{ }^{\circ}\text{C}$ 

TX terminating impedance:

 $Z_{\text{Tx}} = 50 \Omega$ 

ANT terminating impedance:

 $Z_{\text{Ant}} = 50 \Omega \parallel 10 \text{ nH}$ 

RX terminating impedance:

 $Z_{\text{Rx}} = 100 \Omega \text{ (balanced)}$ 

<b>Characteristics Tx-Antenna</b>		<b>min.</b>	<b>typ. @ 25 °C</b>	<b>max.</b>	
<b>Absolute attenuation</b>	$\alpha$				
10.0	... 692.0 MHz	30	46		dB
692.0	... 698.0 MHz	4	10		dB
722.0	... 728.0 MHz	4	13		dB
728.0	... 734.0 MHz	26	37		dB
734.0	... 746.0 MHz	50	57		dB
746.0	... 768.0 MHz	30	48		dB
768.0	... 805.0 MHz	25	44		dB
869.0	... 894.0 MHz	30	44		dB
1408.0	... 1432.0 MHz	30	57		dB
1565.0	... 1607.0 MHz	45	50		dB
1930.0	... 1990.0 MHz	35	43		dB
2110.0	... 2130.0 MHz	27	35		dB
2130.0	... 2170.0 MHz	35	42		dB
2300.0	... 2400.0 MHz	30	40		dB
2400.0	... 2497.0 MHz	32	40		dB
2497.0	... 2690.0 MHz	20	39		dB
2816.0	... 2864.0 MHz	20	38		dB
3300.0	... 3800.0 MHz	20	38		dB
4224.0	... 4296.0 MHz	20	25		dB
4928.0	... 5012.0 MHz	12	18		dB
5150.0	... 5632.0 MHz	12	18		dB
5632.0	... 5728.0 MHz	14	19		dB
5728.0	... 5850.0 MHz	14	21		dB
5850.0	... 6000.0 MHz	14	21		dB

**SAW Components**
**B7924**
**SAW Duplexer**
**710.0 / 740.0 MHz**
**Data sheet**

**Characteristics**

Temperature range for specification:  $T = -30^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$   
 TX terminating impedance:  $Z_{\text{Tx}} = 50 \Omega$   
 ANT terminating impedance:  $Z_{\text{Ant}} = 50 \Omega \parallel 10\text{nH}$   
 RX terminating impedance:  $Z_{\text{Rx}} = 100 \Omega$  (balanced)

Characteristics Antenna-Rx		min.	typ. @ 25 °C	max.	
<b>Center frequency</b>	$f_c$		740		MHz
<b>Maximum insertion attenuation</b>	$\alpha$				
734.0 ... 746.0 MHz			2.2	2.7	dB
<b>Amplitude ripple (p-p)</b>	$\Delta\alpha$				
734.0 ... 746.0 MHz			0.4	1.6	dB
<b>Input VSWR (Ant port)</b>					
734.0 ... 746.0 MHz			1.6	2.0	
<b>Output VSWR (Rx Port)</b>					
734.0 ... 746.0 MHz			1.8	2.0	
<b>Common mode rejection ratio</b>					
734.0 ... 746.0 MHz		23	29		dB
<b>Absolute attenuation</b>	$\alpha$				
10.0 ... 674.0 MHz		35	72		dB
674.0 ... 686.0 MHz		53	72		dB
686.0 ... 704.0 MHz		35	70		dB
704.0 ... 716.0 MHz		55	60		dB
716.0 ... 722.0 MHz		40	65		dB
722.0 ... 724.0 MHz		30	48		dB
724.0 ... 727.0 MHz		15	30		dB
727.0 ... 728.0 MHz		10	24		dB
776.0 ... 805.0 MHz		35	42		dB
1000.0 ... 2300.0 MHz		40	69		dB
2300.0 ... 2690.0 MHz		50	64		dB
2690.0 ... 3300.0 MHz		40	60		dB
3300.0 ... 3800.0 MHz		48	59		dB
3800.0 ... 5150.0 MHz		40	58		dB
5150.0 ... 5850.0 MHz		41	59		dB
5850.0 ... 6000.0 MHz		40	58		dB

**SAW Components**
**B7924**
**SAW Duplexer**
**710.0 / 740.0 MHz**
**Data sheet**

**Characteristics**

Temperature range for specification:	$T = -30^{\circ}\text{C}$ to $+85^{\circ}\text{C}$
TX terminating impedance:	$Z_{\text{Tx}} = 50 \Omega$
ANT terminating impedance:	$Z_{\text{Ant}} = 50 \Omega \parallel 10\text{nH}$
RX terminating impedance:	$Z_{\text{Rx}} = 100 \Omega$ (balanced)



Characteristics Tx-Rx		min.	typ. @ 25 °C	max.	
<b>Differential mode isolation</b>	$\alpha$				
704.0 ... 716.0 MHz		60	65		dB
734.0 ... 738.0 MHz		55	61		dB
738.0 ... 742.0 MHz		55	63		dB
742.0 ... 748.0 MHz		55	61		dB
1408.0 ... 1432.0 MHz		30	74		dB
2112.0 ... 2148.0 MHz		30	64		dB
2816.0 ... 2864.0 MHz		30	62		dB
<b>Common mode isolation</b>	$\alpha$				
704.0 ... 712.0 MHz		48	53		dB
712.0 ... 716.0 MHz		46	51		dB

**Maximum Ratings**


Storage temperature range	$T_{\text{stg}}$	-40/+85	$^{\circ}\text{C}$		
DC voltage	$V_{\text{DC}}$	5	V		
ESD voltage	$V_{\text{ESD}}$	100 <sup>1)</sup>	V	machine model, 1 pulse	
Input power at Tx Port					
706.5 ... 713.5 MHz	$P_{\text{in}}$	28	dBm	}	LTE Up Link Signal
elsewhere	$P_{\text{in}}$	10	dBm		55 °C, 50000h

<sup>1)</sup> According to JESD22-A115A (machine model), 1 negative and 1 positive pulses.


**SAW Components**
**B7924**
**SAW Duplexer**
**710.0 / 740.0 MHz**
**Data sheet**

**Frequency Response TX-ANT**

**Frequency Response TX-ANT**


<b>SAW Components</b>	<b>B7924</b>
<b>SAW Duplexer</b>	<b>710.0 / 740.0 MHz</b>
<b>Data sheet</b>	
<b>Frequency Response ANT-RX</b>	




**Frequency Response ANT-RX**




SAW Components	B7924
SAW Duplexer	710.0 / 740.0 MHz
Data sheet	







### Frequency Response TX-RX



### Frequency Response TX-RX



**SAW Components**
**B7924**
**SAW Duplexer**
**710.0 / 740.0 MHz**
**Data sheet**

**S11 VSWR (TX)**

**S22 VSWR (ANT)**

**S33 VSWR (RX)**


Please read *cautions and warnings* and  
important notes at the end of this document.

<b>SAW Components</b>	<b>B7924</b>
<b>SAW Duplexer</b>	<b>710.0 / 740.0 MHz</b>

Data sheet



References

<b>Type</b>	B7924
<b>Ordering code</b>	B39741B7924P810
<b>Marking and package</b>	C61157-A3-A61
<b>Packaging</b>	F61074-V8153-Z000
<b>Date codes</b>	L_1126
<b>S-parameters</b>	B7924_NB.s4p B7924_WB.s4p
<b>Soldering profile</b>	S_6001
<b>RoHS compatible</b>	Defined as compatible with the following documents: "DIRECTIVE 2002/95/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 27 January 2003 on the restriction of the use of certain hazardous substances in electrical and electronic equipment. 2005/618/EC from April 18th, 2005, amending Directive 2002/95/EC of the European Parliament and of the Council for the purposes of establishing the maximum concentration values for certain hazardous substances in electrical and electronic equipment."
<b>Matching coils</b>	See <a href="http://www.tdk.co.jp/tefe02/coil.htm#aname1">http://www.tdk.co.jp/tefe02/coil.htm#aname1</a> <a href="http://www.tdk.co.jp/etvcl/index.htm">http://www.tdk.co.jp/etvcl/index.htm</a> for a large variety of matching coils.

For further information please contact your local EPCOS sales office or visit our webpage at [www.epcos.com](http://www.epcos.com) .

**Published by EPCOS AG**

**Systems, Acoustics, Waves Business Group**  
**P.O. Box 80 17 09, 81617 Munich, GERMANY**

© EPCOS AG 2011. This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.

Please read *cautions and warnings and important notes* at the end of this document.

## Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that **such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed**.
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.epcos.com/material](http://www.epcos.com/material)). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.epcos.com/trademarks](http://www.epcos.com/trademarks).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EPCOS:

[B39741B7924P810](#)