

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F

ZONE

LTR


DESCRIPTION

DATE


APPD

CM	52				E	REV & REDWN PER EC 0730-0059-95	3-21-95	KS	RS
					E	REVISED PER ECO-09-021510	08SEP09	KK	AEG

- 1 0.00076[.000030] MIN GOLD OVER
0.00127[.000050] MIN NICKEL.
2. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



3 OBSOLETE	GOLD 1	0.20[.008] BRASS	350022-2
	PRE-TIN	0.20[.008] BRASS	350022-1



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON:		DR 3-21-95 K. SALMON	AMP AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ± 0.13[.005]		CHK 3-21-95 R. SWING		
3 PLC DEC ± -		APPD 3-21-95 W. LONG	NAME COMMONING BAR, 4 POSITION	
ANGLES ± -		APPD 3-21-95 W. LONG		
MATERIAL SEE TABLE		PRODUCT SPEC -	SIZE B	CAGE CODE 00779
FINISH SEE TABLE		APPLICATION SPEC -	DRAWING NO C-350022	
		WEIGHT -	SCALE 10:1	SHEET 1 OF 1