




REV.	DATE	DESCRIPTION
A	04/31/03	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S

NOTE:

1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"
OR SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	04/31/03						
7						CHECKED			PART DESCRIPTION N DIRECT SOLDER PLUG (.250” SEMI-RIGID CABLE)					
6						ISSUED								
5						SHEET	1 OF 1		PART NO. 172139					
4	COUPLING NUT	BRASS	NEXCOTE	1										
3	BODY	BRASS	GOLD	1					DWG. NO. 172139.DWG					
2	CONTACT PIN	BRASS	GOLD	1										
1	INSULATOR	TEFLON	NATURAL	1					REV.	A	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/172/172139.DWG							