

CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220, FULL LOAD, +25°C													
		-55°C TO +85°C		-55°C TO +125°C			DC	AC		30 KHz	100 KHz	150 KHz	200 KHz	300 KHz	500 KHz	1 MHz	2 MHz	5 MHz	10 MHz	100 MHz	1 GHz	10 GHz	
		AC	DC	AC	DC																		
SOLDER	10	--	80	--	50	0.008	0.080	--	1.4	15	--	28	--	34	--	44	--	--	60	--	70	--	

PART MARKING:


M15733 / 38-0004
L 0LSP2 DATE CODE

PACKAGE MARKING:


M15733 / 38-0004
0LSP2 DATE CODE
L2 50VDC 10A 125°C
51-359-021
QTY

MARKING NOTES:

N/A



SCHEMATIC



NOTES:

- 1) MOUNTING TORQUE NOT TO EXCEED 7 in-lbs.
- 2) THIS PART CODED "NCA". SCI DOES NOT HAVE CHANGE AUTHORITY. CUSTOMER APPROVAL REQUIRED BEFORE PRODUCT/PROCESS CHANGES CAN BE MADE.

53	52	51	50	REV. NO.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [MILLIMETERS] DO NOT SCALE	TOLERANCES UNLESS OTHERWISE SPECIFIED Dec. .x ± .x Dec. .xx ± .xx Dec. .xxx ± .010 [.25] Angles ± 0° 30"	 FAIRVIEW PENNSYLVANIA Description: LOW PASS EMI FILTER Date: 9-9-11 Engr. B. DEVINE Sheet 1 of 1
CN 60538-ENG	CN 32381-CPD	CN 182252	CN 181539	CHANGE NOTICE NO.	THIRD ANGLE PROJECTION	CODE IDENT. NO. 0LSP2	