


- 1
- FASTON TERMINALS, BASE P/N 63654,
ARE USED IN THIS PRODUCT.
- 2
- TIN PLATE PER MIL-T-10727, 0.002032
[.000080] MIN.



STANDARD	NATURAL	TIN 2	2.29-3.30 [.090-.130]	0.5-1.3 mm ² [20-16]	0.813 [.032]	521284-2
	NATURAL	PLAIN				521284-1
PACKAGING	HOUSING COLOR	TERMINAL FINISH	INSULATION RANGE	WIRE SIZE	MATING TAB THK±0.025 [±.001]	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TERMINAL - BRASS
HOUSING - 6/6 VO NYLON

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.25 [.010]
4 PLC ± -
ANGLES ± -
FINISH

TERMINAL - SEE TABLE
HOUSING - SEE TABLE

DWN
JR RUTH
13MAR00

CHK
MS FEHER
13MAR00

APVD
J HUMMEL
13MAR00

PRODUCT SPEC
118-1285

APPLICATION SPEC
114-2124

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

ASSEMBLY, RECEPTACLE,
ULTRA-POD, 4.8 [.187] SERIES

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=521284

RESTRICTED TO
-

SCALE
5:1

SHEET
1 of 1

REV
D