


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B2	Released as per ECR-09-006012	16-MAR-09	SP	JC
			B3	ECR-13-007945	14MAY2013	KR	TN

TE LOGO, PN, VALUE
TOLERANCE & DATE CODE



- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF
- 3 TECHNICAL SPECIFICATION

DISSIPATION AT 25°C : 10 WATTS MOUNTED
ON STD HEATSINK

BS OHMIC RANGE : R051 TO 7KS


STABILITY : ΔR < =1% PER 1000Hrs

ISOLATION VOLTAGE : 1400V DC/AC pk


MAX WORKING VOLTAGE : 150V DC/AC rms

TEMP COEFFICIENT : > 1R0 50ppm
> 100R 25ppm

CLIMATIC CATEGORY : 55/200/56



RoHS Compliant



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D KENNEDY 07.NOV.05		TE TE Connectivity			
DIMENSIONS: mm		CHK J CATCHPOLE 07.NOV.05					
		APVD J CATCHPOLE 07.NOV.05		NAME HSA 5 METAL CLAD RESISTOR			
		PRODUCT SPEC -		-			
		APPLICATION SPEC -					
MATERIAL -		FINISH -		SIZE A3	CAGE CODE 00779	DRAWING NO C-1625963	RESTRICTED TO -
				Customer Drawing			
				SCALE 4:1	SHEET 1	OF 1	REV B3