



THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Specifications	12-12-07	DP



X(PANEL THICKNESS)	Y(CUTOUT DIMENSION)	Z(CUTOUT DIMENSION)
0.8~1.25 mm	$27.3 \pm 0.2_0$	$31.4 \pm 0.5_0$
1.25~2.0 mm	$27.3 \pm 0.2_0$	$31.6 \pm 0.5_0$



CONTROLLED

NOTES:

RATING: 10A 250V AC
INSULATION RESISTANCE: 100M OHM 500V DC MIN
DIELECTRIC STRENGTH: 2000VAC/1mA ONE MINUTE
APPROVALS: UL, CSA, VDE
DUAL FUSEHOLDER, ONE ACTIVE, ONE SPARE
FUSES NOT INCLUDED - RECOMMENDED SIZE; 5 X 20MM
RoHS COMPLIANT

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number:	723W-X2/03	RoHS Compliant
0-1	0.15	Description:		
1-6	0.20	UNIVERSAL SNAP-IN INLET WITH FUSEHOLDER		
6-18	0.30		UNIT: mm	REV.C
18-50	0.50			
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	B.Zhang 09-09-02	09-09-02	JJH / 09-09-02
250-500	1.20			