







SPECIFICATIONS

VOLTAGE 500Vac
FREQUENCY 50/60Hz
CURRENT 36A @ 40°C
TEMPERATURE -25 TO 100°C
LEAKAGE CURRENT 42mA @ 500V 50Hz
HUMIDITY 90% RH (NON-CONDENSING)
VIBRATION 10-200Hz 1.8G
SURGE 4000Vpk 1.2/50µs
ELECTRIC STRENGTH 2250Vac/1min.
POWER DISSIPATION 16W
MASS 2.7kg
TERMINALS 10sqmm TERMINAL BLOCK
EARTH TERMINALS M6 STUD
FLANGE MOUNTING 4x M6



ALL DIMENSIONS IN MM / ANGLES IN DECIMAL DEGREES



ROXBURGH ELECTRONICS LTD

TITLE 3 PHASE 36A 500V INDUSTRIAL FILTER

Dr No
KMF336-GS

ISSUE

1

GENERAL SPECIFICATION
FOR KMF336

CUSTOMER
REFERENCE

Sheet 1 of 1 Aprvd Date 17/09/97 Aprvd By AT Drwn by AT SCALE CNN--- Location N:\DWG\GS\GS000076

© ROXBURGH ELECTRONICS LTD, FOXHILLS INDUSTRIAL PARK, SCUNTHORPE, NORTH LINCOLNSHIRE, DN15 8QJ TEL +44 1724 281770 F +44 1724 270230