



D





- 1 THE TIPS OF THE POSTS WILL NOT BE PLATED.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 3 .000050-.000150 BRIGHT TIN-LEAD.
- 4 .000050-.000150 MATTE TIN.
- 5 ROHS 2002/95/EC COMPLIANT.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

C



B



A

RECOMMENDED BOARD LAYOUTS

OBSOLETE 6	1	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	7-87194-4
	12	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	7-87194-3
	8	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	7-87194-2
	11	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	7-87194-1
	7	A,D,G,K,N,R,U	7	3.231	3.120	20	21	7-87194-0
	10	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	6-87194-9
	8	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	6-87194-8
	7	A,D,F,J,M,P,S	7	2.763	2.652	17	18	6-87194-7
	6	A,D,G,K,N,R	6	2.607	2.496	16	17	6-87194-6
	8	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	5-87194-5
	5	A,D,G,K,N	5	2.295	2.184	14	15	6-87194-4
	7	A,C,E,G,J,L,N	7	2.139	2.028	13	14	6-87194-3
	4	A,D,J,M	4	1.983	1.872	12	13	6-87194-2
	6	A,C,E,G,J,L	6	1.827	1.716	11	12	6-87194-1
	4	A,D,G,K	4	1.671	1.560	10	11	6-87194-0
	5	A,C,E,G,J	5	1.515	1.404	9	10	5-87194-9
	3	A,D,G	3	1.359	1.248	8	9	5-87194-8
	4	A,C,E,G	4	1.203	1.092	7	8	5-87194-7
	3	A,C,E	3	1.047	.936	6	7	5-87194-6
	3	A,C,E	3	.891	.780	5	6	5-87194-5
OBSOLETE	2	A,D	2	.735	.624	4	5	5-87194-4
	2	A,C	2	.579	.468	3	4	5-87194-3
	1	A	1	.423	.312	2	3	5-87194-2
	1	A	1	.267	.156	1	2	5-87194-1
	11	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	2-87194-4
	12	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	2-87194-3
	8	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	2-87194-2
	11	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	2-87194-1
	7	A,D,G,K,N,R,U	7	3.231	3.120	20	21	2-87194-0
	10	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	1-87194-9
OBSOLETE	8	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	1-87194-8
	7	A,D,F,J,M,P,S	7	2.763	2.652	17	18	1-87194-7
	6	A,D,G,K,N,R	6	2.607	2.496	16	17	1-87194-6
	8	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	1-87194-5
	5	A,D,G,K,N	5	2.295	2.184	14	15	1-87194-4
	7	A,C,E,G,J,L,N	7	2.139	2.028	13	14	1-87194-3
	4	A,D,J,M	4	1.983	1.872	12	13	1-87194-2
	6	A,C,E,G,J,L	6	1.827	1.716	11	12	1-87194-1
	4	A,D,G,K	4	1.671	1.560	10	11	1-87194-0
	5	A,C,E,G,J	5	1.515	1.404	9	10	87194-9
OBSOLETE	3	A,D,G	3	1.359	1.248	8	9	87194-8
	4	A,C,E,G	4	1.203	1.092	7	8	87194-7
	3	A,C,E	3	1.047	.936	6	7	87194-6
	3	A,C,E	3	.891	.780	5	6	87194-5
	2	A,D	2	.735	.624	4	5	87194-4
	2	A,C	2	.579	.468	3	4	87194-3
	1	A	1	.423	.312	2	3	87194-2
	1	A	1	.267	.156	1	2	87194-1
OBSOLETE								
FINISH	KEYWAY LOCATIONS		NO OF KEYWAY	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L A MAYER 14APR87	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK P deJONG 19MAY87	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD P deJONG 19MAY87	PRODUCT SPEC 108-25016	
MATERIAL HOUSING - FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK POSTS-BRASS		FINISH SEE TABLE	SIZE A1	CAGE CODE 00779
WEIGHT -		DRAWING NO 87194	RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV R2		