

NOTES:

① MAT'L: COPPER (STOCK TKN. $\frac{.028}{.79}$)

PLATING: ELECTRO-TIN (.0003 MIN.)

STUD SIZES: (±.005)

02 = .094

04 = 119

 $06 = .146$

08 = 173

10-198

14 - 265


56 = 328

063 - 39
032 - 04

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS= $\frac{\text{INCHES}}{\text{MM}}$

WIRE SIZE: 22-18 AWG
25-1,5 MM²



PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.					AVAILABLE STUD SIZES	
AA-135-	.316 8.03	.303 7.70	.690 17.53					06,08,10	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED				REFERENCE	SCALE:	NTS	DATE	TITLE:	
FAC.	DEC.	ANG.			DRAWN BY:	J ^o	10-17-84	SPADE TONGUE TERMINAL	
±	±	±			CHECKED BY:	GZ	10-18-84	KRIMPTITE 100-SERIES	
					APPROD. BY:				
								EITCmolex INCORPORATED	
								DWG. NO.	A CUSTOMER DWG.