






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P2	REVISED PER ECO-11-004587	11MAR11	RK	HMR




RECOMMENDED HOLE LAYOUT



SECTION X-X

- | | |
|---|--|
|  | FOR 3 POSITION ONLY (.215 WIDE). |
|  | STANDOFFS: UP TO 9 POS—(2 REQD) ON THE OUTSIDE ENDS OF THE HOUSING
10 TO 19 POS—(3 REQD) TWO ON THE OUTSIDE ENDS AND ONE CENTERED ON THE HOUSING
19 POS AND LARGER—(4 REQD) TWO ON THE OUTSIDE ENDS AND TWO SPACED EVENLY
WITHIN THE REMAINING LENGTH OF THE HOUSING. |
|  | POINT OF MEASUREMENT FOR PLATING THICKNESS. |
|  | .000030 GOLD ON THE CONTACT AREA, .000100—.000200 MATTE TIN—LEAD
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL. |
|  | OBsolete PART NUMBER |
|  | RECESSED DATE CODE |
|  | .000030 GOLD ON THE CONTACT AREA, .000100—.000200 MATTE TIN
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL. |
|  | MATERIAL: HOUSING— FLAME RETARDANT THERMOPLASTIC, COLOR— BLACK.
POSTS— COPPER ALLOY |
|  | OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI |

9	OBsolete	7	2.620	2.540	2.400	24	25	7-103414-3
		7	2.520	2.440	2.300	23	24	7-103414-2
9	OBsolete	7	2.420	2.340	2.200	22	23	7-103414-1
		7	2.320	2.240	2.100	21	22	7-103414-0
9	OBsolete	7	2.220	2.140	2.000	20	21	6-103414-9
		7	2.120	2.040	1.900	19	20	6-103414-8
9	OBsolete	7	2.020	1.940	1.800	18	19	6-103414-7
		7	1.920	1.840	1.700	17	18	6-103414-6
9	OBsolete	7	1.820	1.740	1.600	16	17	6-103414-5
		7	1.720	1.640	1.500	15	16	6-103414-4
9	OBsolete	7	1.620	1.540	1.400	14	15	6-103414-3
		7	1.520	1.440	1.300	13	14	6-103414-2
		7	1.420	1.340	1.200	12	13	6-103414-1
		7	1.320	1.240	1.100	11	12	6-103414-0
		7	1.220	1.140	1.000	10	11	5-103414-9
		7	1.120	1.040	.900	9	10	5-103414-8
		7	1.020	.940	.800	8	9	5-103414-7
		7	.920	.840	.700	7	8	5-103414-6
		7	.820	.740	.600	6	7	5-103414-5
		7	.720	.640	.500	5	6	5-103414-4
		7	.620	.540	.400	4	5	5-103414-3
		7	.520	.440	.300	3	4	5-103414-2
		7	.420	.340	.200	2	3	5-103414-1
	OBsolete	4	3.720	3.640	3.500	35	36	3-103414-4
	OBsolete	4	3.620	3.540	3.400	34	35	3-103414-3
	OBsolete	4	3.520	3.440	3.300	33	34	3-103414-2
	OBsolete	4	3.420	3.340	3.200	32	33	3-103414-1
	OBsolete	4	3.320	3.240	3.100	31	32	3-103414-0
	OBsolete	4	3.220	3.140	3.000	30	31	2-103414-9
	OBsolete	4	3.120	3.040	2.900	29	30	2-103414-8
	OBsolete	4	3.020	2.940	2.800	28	29	2-103414-7
	OBsolete	4	2.920	2.840	2.700	27	28	2-103414-6
	OBsolete	4	2.820	2.740	2.600	26	27	2-103414-5
	OBsolete	4	2.720	2.640	2.500	25	26	2-103414-4
9	OBsolete	4	2.620	2.540	2.400	24	25	2-103414-3
		4	2.520	2.440	2.300	23	24	2-103414-2
9	OBsolete	4	2.420	2.340	2.200	22	23	2-103414-1
		4	2.320	2.240	2.100	21	22	2-103414-0
9	OBsolete	4	2.220	2.140	2.000	20	21	1-103414-9
		4	2.120	2.040	1.900	19	20	1-103414-8
9	OBsolete	4	2.020	1.940	1.800	18	19	1-103414-7
		4	1.920	1.840	1.700	17	18	1-103414-6
9	OBsolete	4	1.820	1.740	1.600	16	17	1-103414-5
		4	1.720	1.640	1.500	15	16	1-103414-4
		4	1.620	1.540	1.400	14	15	1-103414-3
		4	1.520	1.440	1.300	13	14	1-103414-2
BY 6-103414-1		4	1.420	1.340	1.200	12	13	1-103414-1
		4	1.320	1.240	1.100	11	12	1-103414-0
		4	1.220	1.140	1.000	10	11	103414-9
		4	1.120	1.040	.900	9	10	103414-8
		4	1.020	.940	.800	8	9	103414-7
		4	.920	.840	.700	7	8	103414-6
		4	.820	.740	.600	6	7	103414-5
		4	.720	.640	.500	5	6	103414-4
		4	.620	.540	.400	4	5	103414-3
		4	.520	.440	.300	3	4	103414-2
		4	.420	.340	.200	2	3	103414-1
					</			

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN R BROWN		28JAN05		 TE Connectivity							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				CHK J GESFORD		28JAN05		NAME					
INCHES						APVD J GESFORD		28JAN05		ASSEMBLY, MOD II, HEADER, SINGLE ROW .100 C/L, (4) SIDED SHROUD					
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —				PRODUCT SPEC —									
MATERIAL		FINISH				APPLICATION SPEC —				SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
		SEE TABLE				WEIGHT —				A1		00779	 103414	—	
CUSTOMER DRAWING								SCALE		4:1		SHEET	1 OF 1	REV	P2