






TII(R) & TIM(R) SERIES

DIMENSIONS






TIM(R)



TIM-10	10	26.56[1.046]	22.86[.900]
TIMR-10	10	26.56[1.046]	22.86[.900]
TIM-09	9	24.02[.946]	20.32[.800]
TIMR-09	9	24.02[.946]	20.32[.800]
TIM-08	8	21.48[.846]	17.78[.700]
TIMR-08	8	21.48[.846]	17.78[.700]
TIM-04	4	11.32[.446]	7.62[.300]
TIMR-04	4	11.32[.446]	7.62[.300]
PROD. NO.	NO. OF POS.	DIM. A	DIM. B

General Tolerance : ±0.2mm


TII(R)



TII-10	10	26.56[1.046]	22.86[.900]
TII-09	9	24.02[.946]	20.32[.800]
TII-08	8	21.48[.846]	17.78[.700]
TII-04	4	11.32[.446]	7.62[.300]
TII-10	10	26.56[1.046]	22.86[.900]
TII-09	9	24.02[.946]	20.32[.800]
TII-08	8	21.48[.846]	17.78[.700]
TII-04	4	11.32[.446]	7.62[.300]
PROD. NO.	NO. OF POS.	DIM. A	DIM. B

General Tolerance : ±0.2mm

HOW TO ORDER



SPECIFICATION

△MECHANICAL
Mechanical Life: 2,000 operations.
Operation Force: 1,000gf max.
Stroke: 0.8 mm
Operation Temp: -20℃ to +85℃
Storage Temperature: -40℃ to +85℃


△ELECTRICAL
Electrical Life: 2,000 cycles.
Rating: 25 mA,24 VDC.
Contact resistance: 100mΩ max.
Dielectric Strength: 500VAC/1 minute.
Circuit: 3 switching positions.

MATERIAL

△BASE & COVER: UL94V-0 Nylon High-Temp Thermoplastic. Color: Black.
△ACTUATOR: UL94V-0 LCP High-Temp Thermoplastic. Color: White.
△CONTACT: Alloy Copper with gold plated.
△TERMINAL: Brass with gold plated.
△TAPE: KAPTON.

SOLDERING PROCESSES


- For best results, please follow these recommendation :
- △ WAVE SOLDERING : Recommended solder temperature at 500°F(260℃) max. 5 seconds for through hole type.
 - △ HAND SOLDERING : Use a soldering iron of 30 watts, controlled at 350℃ approximately max 5 seconds while applying.
 - △ REFLOW SOLDERING : When applying reflow soldering, the peak temperature or the reflow oven should be set at 260℃ max.
 - △ Do not wash the switch body except top tape sealed type, which suitable for spray cleaning method from top of the s/w.
 - △ Any flux enters the switch may fail the conductivity.
 - △ Reflow Temperature Profile :



PACKING


PART NUMBER	Number Per Tube	Number Per Reel
TII(R)-04	41	-
TIM(R)-04		
TII(R)-08	22	-
TIM(R)-08		
TII(R)-09	20	-
TIM(R)-09		
TII(R)-10	18	-
TIM(R)-10		
TII(R)-04.08 09.10	-	900
TIM(R)-04.08 09.10		

TIM(R) TUBE




General Tolerance : ±0.2mm

TII(R) TUBE



General Tolerance : ±0.2mm


TIM(R)-04 REEL



附註								
DMR-06	620160000	24±0.3	11.5±0.1	16.60±0.1	6±0.1	6±0.1	3.5	0.9
DMR-05	620150000	24±0.3	11.5±0.1	14.15±0.1	3±0.1	6±0.1	4.5	0.4
TIM.DMR-04	620140000	24±0.3	11.5±0.1	11.56±0.1	6±0.1	6±0.1	3.5	0.9
DMR-03	620130000	24±0.3	11.5±0.1	9.07±0.1	3±0.1	6±0.1	4.5	0.4
DMR-02	620120000	16±0.3	7.5±0.1	6.50±0.1	3±0.1	6±0.1	3.5	0.9
PART NAME	PART NO:	W±0.3	A	B	C	D	E	F

General Tolerance : ±0.1mm

TIM(R)-08.09.10 REEL



附註								
DMR-12	6201C0000	44.00	20.20	32.00	8.00	6.20	3.45	1.0
TIM.DMR-10	6201A0000	44.00	20.20	26.80	5.0	6.00	4.5	0.4
TIM.DMR-09	620190000	44.00	20.20	24.26	5.00	6.00	4.5	0.4
TIM.DMR-08	620180000	32.00	14.20	21.70	6.00	6.00	3.5	0.9
DMR-07	620170000	32.00	14.20	19.20	5.00	6.00	4.5	0.4
PART NAME	PART NO.	W±0.3	A	B	C	D	E	F

General Tolerance : ±0.1mm