


**FEATURES**

- Extended operating temperature range
- No internal coatings
- No derating or heat sink required to 80°C
- Standard 2-lead TO-46 hermetic package

All surfaces are gold plated. Dimensions are nominal values in inches unless otherwise specified.

ELECTRO-OPTICAL CHARACTERISTICS AT 25°C

PARAMETERS	TEST CONDITIONS	MIN	TYP	MAX	UNITS
Total Power Output, P_o	$I_F = 100\text{mA}$	17	22		mW
Peak Emission Wavelength, λ_p	$I_F = 20\text{mA}$		850		nm
Spectral Bandwidth at 50%, $\Delta\lambda$	$I_F = 20\text{mA}$		40		nm
Half Intensity Beam Angle, θ	$I_F = 20\text{mA}$		8		Deg
Forward Voltage, V_F	$I_F = 100\text{mA}$		1.6	2	Volts
Reverse Breakdown Voltage, V_R	$I_R = 10\mu\text{A}$	5	30		Volts
Rise Time	$I_{FP} = 20\text{mA}$		20		nsec
Fall Time	$I_{FP} = 20\text{mA}$		20		nsec

ABSOLUTE MAXIMUM RATINGS AT 25°C CASE

Power Dissipation ¹	200mW
Continuous Forward Current	100mA
Peak Forward Current ($10\mu\text{s}$, 200Hz) ²	300mA
Reverse Voltage	5V
Lead Soldering Temperature ($1/16"$ from case for 10sec)	260°C

¹Derate per Thermal Derating Curve above 25°C

²Derate linearly above 25°C

THERMAL PARAMETERS

Storage and Operating Temperature Range	-65°C to 150°C
Maximum Junction Temperature	150°C
Thermal Resistance, R_{THJA} ¹	400°C/W Typical
Thermal Resistance, R_{THJA} ²	135°C/W Typical

¹Heat transfer minimized by measuring in still air with minimum heat conducting through leads

²Air circulating at a rapid rate to keep case temperature at 25°C




1260 Calle Suerte, Camarillo, California 93012

Phone: (805) 499-0335, Fax: (805) 499-8108

Email: sales@optodiode.com, Website: www.optodiode.com

MAXIMUM RATINGS



TYPICAL CHARACTERISTICS

