

MultiModem® rCell

Intelligent GPRS Wireless Router




The MultiModem® rCell intelligent wireless router offers standards-based quad-band GPRS performance via the integrated cellular modem. This ready-to-deploy, standalone router integrates seamlessly with virtually any application. The intelligent embedded operating system allows for automatic/persistent connectivity for mission-critical applications and enhanced machine-to-machine (M2M) functionality. The MultiModem rCell intelligent wireless router includes 10/100BaseT Ethernet and RS-232 serial connectivity and can be desktop or panel mounted.

Features

- Quad-band GSM/GPRS
- Models with GPS tracking capability
- NMEA-0183 V3.01 compliant GPS messages
- 10/100BaseT Ethernet LAN connectivity
- RS-232 port for connecting legacy equipment
- Embedded operating system for enhanced M2M functionality
- Stateful Packet Inspection firewall with packet filter rules
- Supports IPSec VPN tunnels for secure LAN-to-LAN access
- 3DES and AES encryption
- Built-in dynamic DNS client
- SMA antenna connector(s) and SIM socket
- Desktop or panel mounting
- FCC, Industry Canada, PTCRB and R&TTE certified
- Web-based management and configuration
- Two-year warranty

Benefits

- Intelligent Embedded OS
- Stateful Packet Inspection firewall
- Supports VPN connections
- Ethernet and RS-232 connectivity
- Carrier approved



Highlights

Applications. The MultiModem rCell intelligent wireless router with GPRS support is ideal for applications which periodically need to send or receive data over a wireless network. For asset tracking and fleet management applications, models with a dedicated GPS receiver are available.

Embedded OS for Enhanced M2M Connectivity. Multi-Tech's embedded operating system provides a web-based programming interface providing easy access to many of the advanced features offered by the MultiModem rCell.

For example, the router can be configured for one of three connectivity modes: always on – when powered on, the router automatically establishes a connection to the wireless network and will re-establish the data link if the connection is lost. Wake-up on ring/Caller ID – this setting allows the router to establish a data link when the router detects an incoming ring or when the router detects an incoming ring based on a particular Caller ID number. Dial-on-demand – when the router is configured for dial on demand, it will establish a data link when LAN activity is detected.

Secure VPN Connections. The MultiModem rCell intelligent wireless router uses the IPSec industry standard protocol, data encryption, and the Internet to provide high performance, secure VPN connections. For LAN-to-LAN connectivity, the MultiModem rCell wireless router utilizes the IPSec protocol to provide tunnels with strong 3DES or AES encryption using IKE and PSK key management. Sized appropriately for M2M applications with support for two concurrent VPN tunnels.

Reduces Development Time. The MultiModem rCell intelligent wireless router can make your existing and next generation device communication-ready without requiring any hardware changes to its design. It actually provides faster time-to-market because it relieves the burden and expense of obtaining PTCRB and RF approvals.

Multiple Interface Options. The MultiModem rCell intelligent wireless router is designed around multiple interface options including Ethernet and RS-232 serial interfaces, to provide you with seamless connectivity for your application. Each interface option offers unique features and benefits related to the technology it supports.

Comprehensive Service and Support. The Multi-Tech commitment to service means we provide a two-year product warranty and service that includes free technical support, 24-hour web site and ftp support.

Specifications

General Features

Quad-band GSM/GPRS, 850/900/1800/1900 MHz

Packet Data Features

GPRS: Class 12 with coding schemes 1-4

GPS

Position: 2.5 meters

Aquisition: Hot start 1 second; cold start 29 seconds avg.

Sensitivity: Tracking -161 dBm

Protocol: NMEA-0183 V3.01, GGA, GLL, GSA, GSV, RMC, VTG

Connectors

LAN: RJ-45, 10/100BaseT

RS-232 Data: DE-9 female, 921.6K bps max serial speed

RF & GPS Antenna: 50 ohm SMA female

Power: 2.5mm miniature screw

SIM: Standard 1.8V & 3V SIM receptacle

Power Requirements

9V to 32VDC

Physical Description

2.8" L x 7.0" W x 1.2" H; 11.5 oz.

(7.1 cm x 17.8 cm x 3.0 cm; 326g)

Environment

Operating: -40° to +185° F (-40° to +85° C)

Storage: -40° to +185° F (-40° to +85° C)

Humidity: 20% to 90% non-condensing

Certifications

CE Mark

EMC: FCC Part 15 Class B, 22, 24; EN 55022 Class B,

EN 301 489-1, EN 301 489-3 (GPS models only),

EN 301 489-7, EN 301 511; RSS 132, 133

Safety: cUL 60950-1, UL 60950-1; IEC 60950-1,

AS/NZS 60950-1

Network: PTCRB

Ordering Information

Product	Description	Region
MTCBA-G2-EN2*	Intelligent GPRS Router	Global
MTCBA-G2-EN2-GP*	Intelligent GPRS Router (GPS)	Global
Ordering Codes		
-NAM	Includes US Style Power Plug	
-EU	Includes Euro Style Power Plug	
-GB/IE	Includes UK Style Power Plug	

* Use ordering codes for specific build options. Go to www.multitech.com for detailed product model numbers.

Produced in the US of US and non-US components.

Features and specifications are subject to change without notice.

Trademarks / Registered Trademarks: MultiModem, Multi-Tech, and the Multi-Tech logo: Multi-Tech Systems, Inc. / All other products and technologies are the trademarks or registered trademarks of their respective holders.

World Headquarters
Tel: (763) 785-3500
(800) 328-9717
www.multitech.com

EMEA Headquarters
Multi-Tech Systems (EMEA)
United Kingdom
Tel: +(44) 118-959 7774