

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [87381-2664](#)
Status: **Active**
Overview: [Milli-Grid™ Connector System](#)
Description: 2.00mm Pitch Milli-Grid™ Receptacle, Surface Mount, Top Entry, 0.38µm Gold (Au) Plating, with Cover, without Locating Pegs, 26 Circuits, Lead-Free

Documents:

- | | |
|--|--|
| 3D Model | RoHS Certificate of Compliance (PDF) |
| Drawing (PDF) | Product Literature (PDF) |
| Product Specification PS-87380-002 (PDF) | |

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	87381
Application	Board-to-Board, Signal
Comments	With Cover
Overview	Milli-Grid™ Connector System
Product Literature Order No	987650-1991
Product Name	Milli-Grid™
UPC	822348483266

Physical

Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.746/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.381µm
Plating min - Termination	1.270µm
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.9A
-------------------------------	------



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[87381Series](#)

Mates With

87758 Vertical, Through Hole, Stackable
PCB Header, 87759 Vertical, Surface
Mount, Stackable PCB Header, 87760
Right Angle, Through Hole, Stackable PCB
Header, 87831 Vertical, Through Hole PCB
Header, 87832 Vertical, Surface Mount PCB

Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	12
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-87380-002
Sales Drawing	SD-87381-**6*

This document was generated on 07/04/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

87381-2664