

5x7mm Surface Mount LVPECL Clock Oscillator

CONNOR WINFIELD



2111 Comprehensive Drive

Aurora, Illinois 60505

Phone: 630-851-4722

Fax: 630-851-5040

www.conwin.com

US Headquarters:

630-851-4722

European Headquarters:

+353-61-472221

Description:

The Connor-Winfield PMxxx - Series are 5x7mm Surface Mount, LVPECL, Fixed Frequency Crystal Controlled Oscillator (XO). The PMxxx - Series are designed for applications requiring tight frequency stability, wide temperature range, and low jitter. Operating at 2.5 or 3.3 Vdc supply voltage, the PMxxx - Series provides LVPECL Differential Outputs with an enable / disable function. The design utilizes PLL multiplication to produce a high frequency output from a low frequency fundamental crystal.



Features:

Model PMxxx - Series

5x7mm Surface Mount Package

2.5 or 3.3 Vdc Operation

LVPECL Differential Outputs

Frequency Stabilities Available:

+/-20 ppm, +/-25 ppm, +/-50 ppm or +/-100 ppm

Temperature Ranges Available:

0 to 70°C, -40 to 85°C, 0 to 85°C or -20 to 70°C

Low Jitter <1ps RMS

Tri-State Enable/Disable on Pad 1

Tape and Reel Packaging

RoHS Compliant / Lead Free

Absolute Maximum Ratings

Parameter	Minimum	Nominal	Maximum	Units	Notes
Storage Temperature	-55	-	125	°C	
Supply Voltage (Vcc)	-0.5	-	4.6	Vdc	
Input Voltage	-0.5	-	Vcc + 0.5	Vdc	

Operating Specifications

Parameter	Minimum	Nominal	Maximum	Units	Notes
Output Frequency (Fo)	98	-	673	MHz	1
Total Frequency Tolerance	(See Ordering Information or Model Matrix for full part number)				
Model PMx4x	-20	-	20	ppm	2
Model PMx1x	-25	-	25	ppm	2
Model PMx2x	-50	-	50	ppm	2
Model PMx3x	-100	-	100	ppm	2
Operating Temperature Range	(See Ordering Information or Model Matrix for full part number)				
Model PM1xx	0	-	70	°C	
Model PM2xx	-40	-	85	°C	
Model PM3xx	0	-	85	°C	
Model PM4xx	-20	-	70	°C	
Supply Voltage (Vcc)	(See Ordering Information or Model Matrix for full part number)				
Model PMxx2	2.375	2.5	2.625	Vdc	
Model PMxx3	3.135	3.3	3.465	Vdc	
Supply Current (Icc)	-	85	95	mA	
Jitter:					
Period Jitter	-	3.0	5.0	ps RMS	
Integrated Phase Jitter	-	0.6	1.0	ps RMS	
SSB Phase Noise (Fo = 155.52 MHz)					
@ 10 Hz offset	-	-40	-	dBc/Hz	
@ 100 Hz offset	-	-75	-	dBc/Hz	
@ 1 KHz offset	-	-95	-	dBc/Hz	
@ 10 KHz offset	-	-110	-	dBc/Hz	
@ 100 KHz offset	-	-115	-	dBc/Hz	
Sub-Harmonics	-	-60	-50	dBc	
Start-Up Time	-	-	2	ms	

Enable / Disable Input Characteristics

Parameter	Minimum	Nominal	Maximum	Units	Notes
Enable Input Voltage - (High) - (Vih)	70%Vcc	-	-	Vdc	3
Disable Input Voltage - (Low) - (Vil)	-	-	30%Vcc	Vdc	3

LVPECL Output Characteristics

Parameter	Minimum	Nominal	Maximum	Units	Notes
Load	-	50	-	Ohm	4
Voltage (High) (Voh)	Vcc-1.025	-	-	V	
(Low) (Vol)	-	-	Vcc-1.620	V	
Duty Cycle at 50% Level	45	50	55	%	5
Rise / Fall Time: 20% to 80%	-	0.3	0.6	ns	

Package Characteristics

Package: Hermetically sealed ceramic package and metal cover

Environmental Characteristics

Vibration: Vibration per Mil Std 883E Method 2007.3 Test Condition A.

Shock: Mechanical Shock per Mil Std 883E Method 2002.4 Test Condition B.

Soldering Process: RoHS compliant lead free. See soldering profile on page 2.

Notes:

1. All output frequencies may not be available, please contact the factory with your output frequency requirements.

2. Includes calibration @ 25°C, frequency stability vs. change in temperature, supply voltage and load variations, shock and vibration and 20 years aging.

3. When the oscillator is disabled the outputs are at high impedance. Outputs are enabled with no connection on E/D pad 1.

4. Outputs must be terminated into 50 ohms to Vcc - 2V or Thevenin equivalent.

5. Duty cycle measured at 50% of output voltage swing.

Specifications subject to change without notice. All dimensions in inches. © Copyright 2010 The Connor-Winfield Corporation



Bulletin **Ec262**
Page **1 of 2**
Revision **01**
Date **10 Mar 2011**

