


M57732L

135-160MHz, 12.5V, 7W, FM PORTABLE RADIO


OUTLINE DRAWING

Dimensions in mm



H12

BLOCK DIAGRAM



PIN :

- ① Pin : RF INPUT
- ② Vcc1 : 1st. DC SUPPLY
- ③ VBB : BASE BIAS SUPPLY
- ④ Vcc2 : 2nd. DC SUPPLY
- ⑤ Po : RF OUTPUT
- ⑥ GND : FIN

ABSOLUTE MAXIMUM RATINGS (T_c = 25°C unless otherwise noted)

Symbol	Parameter	Conditions	Ratings	Unit
V _{cc}	Supply voltage		16	V
V _{BB}	Base bias		6	V
I _{cc}	Total current		4	A
P _{in(max)}	Input power	V _{cc1} = 12.5V, Z _G = Z _L = 50 Ω	40	mW
P _{o(max)}	Output power	Z _G = Z _L = 50 Ω	10	W
T _{c(OP)}	Operation case temperature		- 30 to 110	°C
T _{stg}	Storage temperature		- 40 to 110	°C

Note. Above parameters are guaranteed independently.


ELECTRICAL CHARACTERISTICS (T_c = 25°C unless otherwise noted)

Symbol	Parameter	Test conditions	Limits		Unit
			Min	Max	
f	Frequency range	V _{cc1} = V _{cc2} = 12.5V V _{BB} = 5V P _{in} = 20mW Z _G = Z _L = 50 Ω	135	160	MHz
P _o	Output power		7		W
η _T	Total efficiency		40		%
2f _o	2nd. harmonic			- 20	dBc
3f _o	3rd. harmonic			- 30	dBc
ρ _{in}	Input VSWR			2.5	-
-	Load VSWR tolerance	V _{cc1} = V _{cc2} = 13.2V, V _{BB} = 5V P _o = 7W (P _{in} : controlled) Load VSWR = 20 : 1 (All phase) Z _G = 50Ω	No degradation or destroy		-


Note. Above parameters, ratings, limits and conditions are subject to change.

TYPICAL PERFORMANCE DATA


OUTPUT POWER, TOTAL EFFICIENCY, INPUT VSWR
VS. FREQUENCY CHARACTERISTICS




OUTPUT POWER, TOTAL EFFICIENCY, INPUT VSWR
VS. FREQUENCY CHARACTERISTICS




OUTPUT POWER, TOTAL EFFICIENCY, INPUT VSWR
VS. FREQUENCY CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. INPUT POWER
CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. INPUT POWER
CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. INPUT POWER
CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. SUPPLY VOLTAGE
CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. SUPPLY VOLTAGE
CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
1st CURRENT VS. SUPPLY VOLTAGE
CHARACTERISTICS



OUTPUT POWER, 2nd CURRENT VS.
1st SUPPLY VOLTAGE CHARACTERISTICS



OUTPUT POWER, 2nd CURRENT VS.
1st SUPPLY VOLTAGE CHARACTERISTICS



OUTPUT POWER, 2nd CURRENT VS.
1st SUPPLY VOLTAGE CHARACTERISTICS

