

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT

By -

ALL RIGHTS RESERVED

LOC

DIST	
------	--

A

39

REVISIONS

P	I
---	---

LIR

DESCRIPTION

DAT

DWRN

APVE

R

REVI

SED E


ER FO

0-14-00006


26A

4	NH
---	----

	MM
--	----




- | | |
|---|---|
| 1 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 2 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 3 | PACKAGE IN SINGLE TUBES |
| 4 | .000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL. |
| 5 | .000100-.000200 BRIGHT TIN OVER .000050 NICKEL. |
| 6 | PRELIMINARY PART - NOT RELEASED FOR PRODUCTION. |
| 7 | HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK. |
| 8 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



RECOMMENDED HOLE LAYOUT

OBSOLETE		5			.484	.400	4	5	5-103321-3
		5		6	1.384	1.300	13	14	5-103321-2
		5		6	1.184	1.100	11	12	5-103321-1
		5		6	1.084	1.000	10	11	5-103321-0
		5		6	.884	.800	8	9	4-103321-9
		5			3.984	3.900	39	40	4-103321-8
		5			1.584	1.500	15	16	4-103321-7
		5			.784	.700	7	8	4-103321-6
		5			.284	.200	2	3	4-103321-5
		5			.184	.100	1	2	4-103321-4
		5		6	.084	—	—	1	4-103321-3
SUPERSEDED BY 1-103321-4				3	1.384	1.300	13	14	4-103321-2
SUPERSEDED BY 103321-3				3	.284	.200	2	3	4-103321-1
		4			3.984	3.900	39	40	4-103321-0
A	OBSOLETE	4			3.884	3.800	38	39	3-103321-9
A	OBSOLETE	4			3.784	3.700	37	38	3-103321-8
A	OBSOLETE	4			3.684	3.600	36	37	3-103321-7
		4			3.584	3.500	35	36	3-103321-6
A	OBSOLETE	4			3.484	3.400	34	35	3-103321-5
A	OBSOLETE	4			3.384	3.300	33	34	3-103321-4
A	OBSOLETE	4			3.284	3.200	32	33	3-103321-3
A	OBSOLETE	4			3.184	3.100	31	32	3-103321-2
A	OBSOLETE	4			3.084	3.000	30	31	3-103321-1
A	OBSOLETE	4			2.984	2.900	29	30	3-103321-0
A	OBSOLETE	4			2.884	2.800	28	29	2-103321-9
A	OBSOLETE	4			2.784	2.700	27	28	2-103321-8
A	OBSOLETE	4			2.684	2.600	26	27	2-103321-7
A	OBSOLETE	4			2.584	2.500	25	26	2-103321-6
		4			2.484	2.400	24	25	2-103321-5
A	OBSOLETE	4			2.384	2.300	23	24	2-103321-4
A	OBSOLETE	4			2.284	2.200	22	23	2-103321-3
A	OBSOLETE	4			2.184	2.100	21	22	2-103321-2
A	OBSOLETE	4			2.084	2.000	20	21	2-103321-1
A	SUPERSEDED BY 7-146274-0	4			1.984	1.900	19	20	2-103321-0
A	OBSOLETE	4			1.884	1.800	18	19	1-103321-9
A	OBSOLETE	4			1.784	1.700	17	18	1-103321-8
A	OBSOLETE	4			1.684	1.600	16	17	1-103321-7
		4			1.584	1.500	15	16	1-103321-6
A	OBSOLETE	4			1.484	1.400	14	15	1-103321-5
		4			1.384	1.300	13	14	1-103321-4
A	OBSOLETE	4			1.284	1.200	12	13	1-103321-3
A	OBSOLETE	4			1.184	1.100	11	12	1-103321-2
A	OBSOLETE	4			1.084	1.000	10	11	1-103321-1
		4			.984	.900	9	10	1-103321-0
		4			.884	.800	8	9	103321-9

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN. 150C192 CHG. 23NOV92		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DRAWN BY JOHN KNITTLE APP'D BY B. FLINCHBAUGH	NAME		ASSEMBLY, HEADER, BREAKAWAY, MOD II, SINGLE ROW, .100 C/L, VERTICAL, WITH .025 SQUARE POSTS		
				PRODUCT SPEC					
				APPLICATION SPEC					
MATERIAL POST: COPPER ALLOY	FINISH SEE TABLE		WEIGHT —		SIZE A1	CAGE CODE 00779	DRAWING NO. C=103321	RESTRICTED ? —	
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1	REV —