


SWITCHING APPLICATION.  
INTERFACE CIRCUIT AND DRIVER CIRCUIT APPLICATION.

### FEATURES


- With Built-in Bias Resistors.
- Simplify Circuit Design.
- Reduce a Quantity of Parts and Manufacturing Process.

### EQUIVALENT CIRCUIT



### BIAS RESISTOR VALUES

| TYPE NO. | R1(k $\Omega$ ) | R2(k $\Omega$ ) |
|----------|-----------------|-----------------|
| KRC101S  | 4.7             | 4.7             |
| KRC102S  | 10              | 10              |
| KRC103S  | 22              | 22              |
| KRC104S  | 47              | 47              |
| KRC105S  | 2.2             | 47              |
| KRC106S  | 4.7             | 47              |




### MAXIMUM RATINGS (Ta=25℃)

| CHARACTERISTIC            |               | SYMBOL           | RATING  | UNIT |
|---------------------------|---------------|------------------|---------|------|
| Output Voltage            | KRC101S ~106S | V <sub>O</sub>   | 50      | V    |
| Input Voltage             | KRC101S       | V <sub>I</sub>   | 20, -10 | V    |
|                           | KRC102S       |                  | 30, -10 |      |
|                           | KRC103S       |                  | 40, -10 |      |
|                           | KRC104S       |                  | 40, -10 |      |
|                           | KRC105S       |                  | 12, -5  |      |
|                           | KRC106S       |                  | 20, -5  |      |
| Output Current            | KRC101S ~106S | I <sub>O</sub>   | 100     | mA   |
| Power Dissipation         |               | P <sub>D</sub>   | 200     | mW   |
| Junction Temperature      |               | T <sub>j</sub>   | 150     | ℃    |
| Storage Temperature Range |               | T <sub>stg</sub> | -55~150 | ℃    |

### MARK SPEC

| TYPE | KRC101S | KRC102S | KRC103S | KRC104S | KRC105S | KRC106S |
|------|---------|---------|---------|---------|---------|---------|
| MARK | NA      | NB      | NC      | ND      | NE      | NF      |

### Marking



# KRC101S ~ KRC106S

## ELECTRICAL CHARACTERISTICS (Ta=25°C)

| CHARACTERISTIC         |              | SYMBOL       | TEST CONDITION        | MIN. | TYP. | MAX. | UNIT |
|------------------------|--------------|--------------|-----------------------|------|------|------|------|
| Output Cut-off Current | KRC101S~106S | $I_{O(OFF)}$ | $V_O=50V, V_I=0$      | -    | -    | 500  | nA   |
| DC Current Gain        | KRC101S      | $G_I$        | $V_O=5V, I_O=10mA$    | 30   | 55   | -    |      |
|                        | KRC102S      |              |                       | 50   | 80   | -    |      |
|                        | KRC103S      |              |                       | 70   | 120  | -    |      |
|                        | KRC104S      |              |                       | 80   | 200  | -    |      |
|                        | KRC105S      |              |                       | 80   | 200  | -    |      |
|                        | KRC106S      |              |                       | 80   | 200  | -    |      |
| Output Voltage         | KRC101S~106S | $V_{O(ON)}$  | $I_O=10mA, I_I=0.5mA$ | -    | 0.1  | 0.3  | V    |
| Input Voltage (ON)     | KRC101S      | $V_{I(ON)}$  | $V_O=0.2V, I_O=5mA$   | -    | 1.5  | 2.0  | V    |
|                        | KRC102S      |              |                       | -    | 1.8  | 2.4  |      |
|                        | KRC103S      |              |                       | -    | 2.1  | 3.0  |      |
|                        | KRC104S      |              |                       | -    | 2.8  | 5.0  |      |
|                        | KRC105S      |              |                       | -    | 0.8  | 1.1  |      |
|                        | KRC106S      |              |                       | -    | 0.9  | 1.3  |      |
| Input Voltage (OFF)    | KRC101S~104S | $V_{I(OFF)}$ | $V_O=5V, I_O=0.1mA$   | 1.0  | 1.2  | -    | V    |
|                        | KRC105S~106S |              |                       | 0.5  | 0.65 | -    |      |
| Transition Frequency   | KRC101S~106S | $f_T *$      | $V_O=10V, I_O=5mA$    | -    | 200  | -    | MHz  |
| Input Current          | KRC101S      | $I_I$        | $V_I=5V$              | -    | -    | 1.8  | mA   |
|                        | KRC102S      |              |                       | -    | -    | 0.88 |      |
|                        | KRC103S      |              |                       | -    | -    | 0.36 |      |
|                        | KRC104S      |              |                       | -    | -    | 0.18 |      |
|                        | KRC105S      |              |                       | -    | -    | 3.6  |      |
|                        | KRC106S      |              |                       | -    | -    | 1.8  |      |







Note : \*Characteristic of Transistor Only

# KRC101S ~ KRC106S







## ELECTRICAL CHARACTERISTICS (Ta=25°C)

| CHARACTERISTIC |              |         | SYMBOL    | TEST CONDITION                            | MIN. | TYP. | MAX. | UNIT    |
|----------------|--------------|---------|-----------|-------------------------------------------|------|------|------|---------|
| Switching Time | Rise Time    | KRC101S | $t_r$     | $V_O=5V$<br>$V_{IN}=5V$<br>$R_L=1k\Omega$ | –    | 0.03 | –    | $\mu S$ |
|                |              | KRC102S |           |                                           | –    | 0.05 | –    |         |
|                |              | KRC103S |           |                                           | –    | 0.12 | –    |         |
|                |              | KRC104S |           |                                           | –    | 0.22 | –    |         |
|                |              | KRC105S |           |                                           | –    | 0.01 | –    |         |
|                |              | KRC106S |           |                                           | –    | 0.03 | –    |         |
|                | Storage Time | KRC101S | $t_{sig}$ |                                           | –    | 2.0  | –    |         |
|                |              | KRC102S |           |                                           | –    | 2.0  | –    |         |
|                |              | KRC103S |           |                                           | –    | 2.0  | –    |         |
|                |              | KRC104S |           |                                           | –    | 2.0  | –    |         |
|                |              | KRC105S |           |                                           | –    | 2.0  | –    |         |
|                |              | KRC106S |           |                                           | –    | 2.0  | –    |         |
|                | Fall Time    | KRC101S | $t_f$     |                                           | –    | 0.12 | –    |         |
|                |              | KRC102S |           |                                           | –    | 0.36 | –    |         |
|                |              | KRC103S |           |                                           | –    | 0.35 | –    |         |
|                |              | KRC104S |           |                                           | –    | 0.6  | –    |         |
|                |              | KRC105S |           |                                           | –    | 0.1  | –    |         |
|                |              | KRC106S |           |                                           | –    | 0.19 | –    |         |

# KRC101S ~ KRC106S



# KRC101S ~ KRC106S



# KRC101S ~ KRC106S

