






RECOMENDED PC BOARD MOUNTING DIMENSIONS  
FOR .063 [.160] THICK PC BOARD AND  
.012 [.305] STENCIL THICK.

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

DWN

APVD

AD

00

F

LTR

DESCRIPTION

DATE

DWN

APVD

C

SEE SHEET 1

-

-

-

6

1,2,39,40

101.19  
[3.984]

99.06  
[3.900]

39

40

9-146307-0

6

1,2,38,39

98.65  
[3.884]

96.52  
[3.800]

38

39

8-146307-9

6

1,2,37,38

96.11  
[3.684]

93.98  
[3.700]

37

38

8-146307-8

6

1,2,36,37

93.57  
[3.684]

91.44  
[3.600]

36

37

8-146307-7

6

1,2,35,36

91.03  
[3.584]

88.90  
[3.500]

35

36

8-146307-6

6

1,2,34,35

88.49  
[3.484]

86.36  
[3.400]

34

35

8-146307-5

6

1,2,33,34

85.95  
[3.384]

83.82  
[3.300]

33

34

8-146307-4

6

1,2,32,33

83.41  
[3.284]

81.28  
[3.200]

32

33

8-146307-3

6

1,2,31,32

80.87  
[3.184]

78.74  
[3.100]

31

32

8-146307-2

6

1,2,30,31

78.33  
[3.084]

76.20  
[3.000]

30

31

8-146307-1

6

1,2,29,30

75.79  
[2.984]

73.66  
[2.900]

29

30

8-146307-0

6

1,2,28,29

73.25  
[2.884]

71.12  
[2.800]

28

29

7-146307-9

6

1,2,27,28

70.71  
[2.684]

68.58  
[2.700]

27

28

7-146307-8

6

1,2,26,27

68.17  
[2.684]

66.04  
[2.600]

26

27

7-146307-7

6

1,2,25,26

65.63  
[2.584]

63.5  
[2.500]

25

26

7-146307-6

6

1,2,24,25

63.09  
[2.484]

60.96  
[2.400]

24

25

7-146307-5

6

1,2,23,24

60.55  
[2.384]

58.42  
[2.300]

23

24

7-146307-4

6

1,2,22,23

58.01  
[2.284]

55.88  
[2.200]

22

23

7-146307-3

6

1,2,21,22

55.47  
[2.184]

53.34  
[2.100]

21

22

7-146307-2

6

1,2,20,21

52.93  
[2.084]

50.80  
[2.000]

20

21

7-146307-1

6

1,2,19,20

50.39  
[1.984]

48.26  
[1.900]

19

20

7-146307-0

6

1,2,18,19

47.85  
[1.884]

45.72  
[1.800]

18

19

6-146307-9

6

1,2,17,18

45.31  
[1.784]

43.18  
[1.700]

17

18

6-146307-8

6

1,2,16,17

42.77  
[1.584]

40.64  
[1.600]

16

17

6-146307-7

6

1,2,15,16

40.23  
[1.584]

38.10  
[1.500]

15

16

6-146307-6

6

1,2,14,15

37.69  
[1.484]

35.56  
[1.400]

14

15

6-146307-5

6

1,2,13,14

35.15  
[1.384]

33.02  
[1.200]

13

14

6-146307-4

6

1,2,12,13

32.61  
[1.284]

30.48  
[1.200]

12

13

6-146307-3

6

1,2,11,12

30.07  
[1.184]

27.94  
[1.100]

11

12

6-146307-2

6

1,2,10,11

27.53  
[1.084]

25.40  
[1.000]

10

11

6-146307-1

6

1,2,9,10

24.99  
[.984]

22.86  
[.900]

9

10

6-146307-0

6

1,2,8,9

22.45  
[.884]

20.32  
[.800]

8

9

5-146307-9

6

1,2,7,8

19.91  
[.784]

17.78  
[.700]

7

8

5-146307-8

6

1,2,6,7

17.37  
[.684]

15.24  
[.600]

6

7

5-146307-7

6

ALL

14.83  
[.584]

12.70  
[.500]

5

6

5-146307-6

6

ALL

12.29  
[.484]

10.16  
[.400]

4

5

5-146307-5

6

ALL

9.75  
[.384]

7.62  
[.300]

3

4

5-146307-4

6

ALL

7.21  
[.284]

5.08  
[.200]

2

3

5-146307-3

PLATING

HOLD-DOWN POST  
CONFIG. LOCATIONS.

C

B

A

NO. OF  
POSITIONS

PART NUMBER

4

1,2,39,40

101.19  
[3.984]

99.06  
[3.900]

39

40

4-146307-0

4

1,2,38,39

98.65  
[3.884]

96.52  
[3.800]

38

39

3-146307-9

4

1,2,37,38

96.11  
[3.684]

93.98  
[3.700]

37

38

3-146307-8

4

1,2,36,37

93.57  
[3.684]

91.44  
[3.600]

36

37

3-146307-7

4

1,2,35,36

91.03  
[3.584]

88.90  
[3.500]

35

36

3-146307-6

4

1,2,34,35

88.49  
[3.484]

86.36  
[3.400]

34

35

3-146307-5

4

1,2,33,34

85.95  
[3.384]

83.82  
[3.300]

33

34

3-146307-4

4

1,2,32,33

83.41  
[3.284]

81.28  
[3.200]

32

33

3-146307-3

4

1,2,31,32

80.87  
[3.184]

78.74  
[3.100]

31

32

3-146307-2

4

1,2,30,31

78.33  
[3.084]

76.20  
[3.000]

30

31

3-146307-1

4

1,2,29,30

75.79  
[2.984]

73.66  
[2.900]

29

30

3-146307-0

4

1,2,28,29

73.25  
[2.884]

71.12  
[2.800]

28

29

2-146307-9

4

1,2,27,28

70.71  
[2.684]

68.58  
[2.700]

27

28

2-146307-8

4

1,2,26,27

68.17  
[2.684]

66.04  
[2.600]

26

27

2-146307-7

4

1,2,25,26

65.63  
[2.584]

63.5  
[2.500]

25

26

2-146307-6

4

1,2,24,25

63.09  
[2.484]

60.96  
[2.400]

24

25

2-146307-5

4

1,2,23,24

60.55  
[2.384]

58.42  
[2.300]

23

24

2-146307-4

4

1,2,22,23

58.01  
[2.284]

55.88  
[2.200]

22

23

2-146307-3

4

1,2,21,22

55.47  
[2.184]

53.34  
[2.100]

21

22

2-146307-2

4

1,2,20,21

52.93  
[2.084]

50.80  
[2.000]

20

21

2-146307-1

4

1,2,19,20

50.39  
[1.984]

48.26  
[1.900]

19

20

2-146307-0

4

1,2,18,19

47.85  
[1.884]

45.72  
[1.800]

18

19

1-146307-9

4

1,2,17,18

45.31  
[1.784]

43.18  
[1.700]

17

18

1-146307-8

4

1,2,16,17

42.77  
[1.584]

40.64  
[1.600]

16

17

1-146307-7

4

1,2,15,16

40.23  
[1.584]

38.10  
[1.500]

15

16

1-146307-6

4

1,2,14,15

37.69  
[1.484]

35.56  
[1.400]

14

15

1-146307-5

4

1,2,13,14

35.15  
[1.384]

33.02  
[1.200]

13

14

1-146307-4

4

1,2,12,13

32.61  
[1.284]

30.48  
[1.200]

12

13

1-146307-3

4

1,2,11,12

30.07  
[1.184]

27.94  
[1.100]

11

12

1-146307-2

4

1,2,10,11

27.53  
[1.084]

25.40  
[1.000]

10

11

1-146307-1

4

1,2,9,10

24.99  
[.984]

22.86  
[.900]

9

10

1-146307-0

4

1,2,8,9

22.45  
[.884]

20.32  
[.800]

8

9

146307-9

4

1,2,7,8

19.91  
[.784]

17.78  
[.700]

7

8

146307-8

4

1,2,6,7

17.37  
[.684]

15.24  
[.600]

6

7

146307-7

4

ALL

14.83  
[.584]

12.70  
[.500]

5

6

146307-6

4

ALL

12.29  
[.484]

10.16  
[.400]

4

5

146307-5

4

ALL

9.75  
[.384]

7.62  
[.300]

3

4

146307-4

4

ALL

7.21  
[.284]

5.08  
[.200]

2

3

146307-3

4

-

4.67  
[.184]

2.54  
[.100]

1

2

146307-2

4

-

2.13  
[.084]

[ - ]

0

1

146307-1

PLATING

HOLD-DOWN POST  
CONFIG. LOCATIONS.

C

B

A

NO. OF  
POSITIONS

PART NUMBER

7

1,2,39,40

101.19  
[3.984]

99.06  
[3.900]

39

40

9-146307-0

7

1,2,38,39

98.65  
[3.884]

96.52  
[3.800]

38

39

8-146307-9

7

1,2,37,38

96.11  
[3.684]

93.98  
[3.700]

37

38

8-146307-8

7

1,2,36,37

93.57  
[3.684]

91.44  
[3.600]

36

37

8-146307-7

7

1,2,35,36

91.03  
[3.584]

88.90  
[3.500]

35

36

8-146307-6

7

1,2,34,35

88.49  
[3.484]

86.36  
[3.400]

34

35

8-146307-5

7

1,2,33,34

85.95  
[3.384]

83.82  
[3.300]

33

34

8-146307-4

7

1,2,32,33

83.41  
[3.284]

81.28  
[3.200]

32

33

8-146307-3

7

1,2,31,32

80.87  
[3.184]

78.74  
[3.100]

31

32

8-146307-2

7

1,2,30,31

78.33  
[3.084]

76.20  
[3.000]

30

31

8-146307-1

7

1,2,29,30

75.79  
[2.984]

73.66  
[2.900]

29

30

8-146307-0

7

1,2,28,29

73.25  
[2.884]

71.12  
[2.800]

28

29

7-146307-9

7

1,2,27,28

70.71  
[2.684]

68.58  
[2.700]

27

28

7-146307-8

7

1,2,26,27

68.17  
[2.684]

66.04  
[2.600]

26

27

7-146307-7

7

1,2,25,26

65.63  
[2.584]

63.5  
[2.500]

25

26

7-146307-6

7

1,2,24,25

63.09  
[2.484]

60.96  
[2.400]

24

25

7-146307-5

7

1,2,23,24

60.55  
[2.384]

58.42  
[2.300]

23

24

7-146307-4

7

1,2,22,23

58.01  
[2.284]

55.88  
[2.200]

22

23

7-146307-3

7

1,2,21,22

55.47  
[2.184]

53.34  
[2.100]

21

22

7-146307-2

7

1,2,20,21

52.93  
[2.084]

50.80  
[2.000]

20

21

7-146307-1

7

1,2,19,20

50.39  
[1.984]

48.26  
[1.900]

19

20

7-146307-0

7

1,2,18,19

47.85  
[1.884]

45.72  
[1.800]

18

19

6-146307-9

7

1,2,17,18

45.31  
[1.784]

43.18  
[1.700]

17

18

6-146307-8

7

1,2,16,17

42.77  
[1.584]

40.64  
[1.600]

16

17

6-146307-7

7

1,2,15,16

40.23  
[1.584]

38.10  
[1.500]

15

16

6-146307-6

7

1,2,14,15

37.69  
[1.484]

35.56  
[1.400]

14

15

6-146307-5

7

1,2,13,14

35.15  
[1.384]

33.02  
[1.200]

13

14

6-146307-4

7

1,2,12,13

32.61  
[1.284]

30.48  
[1.200]

12

13

6-146307-3

7

1,2,11,12

30.07  
[1.184]

27.94  
[1.100]

11

12

6-146307-2

7

1,2,10,11

27.53  
[1.084]

25.40  
[1.000]

10

11

6-146307-1

7

1,2,9,10

24.99  
[.984]

22.86  
[.900]

9

10

6-146307-0

7

1,2,8,9

22.45  
[.884]

20.32  
[.800]

8

9

5-146307-9

7

1,2,7,8

19.91  
[.784]

17.78  
[.700]

7

8

5-146307-8

7

1,2,6,7

17.37  
[.684]

15.24  
[.600]

6

7

5-146307-7

7

ALL

14.83  
[.584]

12.70  
[.500]

5

6

5-146307-6

7

ALL

12.29  
[.484]

10.16  
[.400]

4

5

5-146307-5

7

ALL

9.75  
[.384]

7.62  
[.300]

3

4

5-146307-4

7

ALL

7.21  
[.284]

5.08  
[.200]

2

3

5-146307-3

PLATING

HOLD-DOWN POST  
CONFIG. LOCATIONS.

C

B

A

NO. OF  
POSITIONS

PART NUMBER

5

1,2,39,40

101.19  
[3.984]

99.06  
[3.900]

39

40

9-146307-0

5

1,2,38,39

98.65  
[3.884]

96.52  
[3.800]

38

39

8-146307-9

5

1,2,37,38

96.11  
[3.684]

93.98  
[3.700]

37

38

8-146307-8

5

1,2,36,37

93.57  
[3.684]

91.44  
[3.600]

36

37

8-146307-7

5

1,2,35,36

91.03  
[3.584]

88.90  
[3.500]

35

36

8-146307-6

5

1,2,34,35

88.49  
[3.484]

86.36  
[3.400]

34

35

8-146307-5

5

1,2,33,34

85.95  
[3.384]

83.82  
[3.300]

33

34

8-146307-4

5

1,2,32,33

83.41  
[3.284]

81.28  
[3.200]

32

33

8-146307-3

5

1,2,31,32

80.87  
[3.184]

78.74  
[3.100]

31

32

8-146307-2

5

1,2,30,31

78.33  
[3.084]

76.20  
[3.000]

30

31

8-146307-1

5

1,2,29,30

75.79  
[2.984]

73.66  
[2.900]

29

30

8-146307-0

5

1,2,28,29

73.25  
[2.884]

71.12  
[2.800]

28

29

7-146307-9

5

1,2,27,28

70.71  
[2.684]

68.58  
[2.700]

27

28

7-146307-8

5

1,2,26,27

68.17  
[2.684]

66.04  
[2.600]

26

27

7-146307-7

5

1,2,25,26

65.63  
[2.584]

63.5  
[2.500]

25

26

7-146307-6

5

1,2,24,25

63.09  
[2.484]

60.96  
[2.400]

24

25

7-146307-5

5

1,2,23,24

60.55  
[2.384]

58.42  
[2.300]

23

24

7-146307-4

5

1,2,22,23

58.01  
[2.284]

55.88  
[2.200]

22

23

7-146307-3

5

1,2,21,22

55.47  
[2.184]

53.34  
[2.100]

21

22

7-146307-2

5

1,2,20,21

52.93  
[2.084]

50.80  
[2.000]

20

21

7-146307-1

5

1,2,19,20

50.39  
[1.984]

48.26  
[1.900]

19

20

7-146307-0

5

<