

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		REVISIONS					
© COPYRIGHT — TE Connectivity		ALL RIGHTS RESERVED.		P	LTR	DESCRIPTION	DATE	DWN	APVD
					AB	REV PER 0G3A-0674-04	25AUG04	JR	TM
					AB1	REVISED PER ECO-17-006294	12OCT2017	RS	DR
STAMPING DETAIL SA AMP 2214 VS UL 1 FOR Ø5.969 [Ø.235] MAX WIRE INSULATION. 2 MATERIAL: BODY — COPPER INSULATION — PVC 19.685 [.775] MAX									

PURPLE

COLOR

1000

QTY

LOOSE PIECE

DESCRIPTION

2-328375-3

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
90°C[194°F]

VOLTAGE RATING:
300V MAX

CIRCULAR MIL AREA:
0.26-2.62mm²[509-5180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

2

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ± -

FINISH -

DWN
S. GOULDEN
1-27-93

CHK
R HERSEY
1-27-93

APVD
M ELLIS
1-27-93

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

STE

TE Connectivity

NAME

SPLICE, WIRE, CLOSED END
22-14 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=328375

—

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
AB1