



## FLIR E4, E5, E6, E8 with MSX® Enhancement

FLIR E4, E5, E6, E8 with MSX® Enhancement

- Display: 3" color LCD
- On-board 640 x 480 Digital Camera
- Easy-to-use, weighs only 1.2lbs
- 2% accuracy
- File format: Radiometric jpg
- Swappable Li-ion Battery with 4 hour life
- Spot Measurement mode
- Simultaneous storage of IR/Visual/MSX images
- Picture in Picture image (E5, E6 and E8)
- Area Box Measurement mode (E5, E6 and E8)

Each includes power supply/charger with four plugs, rechargeable battery, FLIR Tools software, USB cable, and hard transport case. E8 also includes extra battery and external battery charger.

FLIR E4

- 4800 pixels (80 x 60)

FLIR E5

- 10,800 pixels (120 x 90)

FLIR E6

- 19,200 pixels (160 x 120)

FLIR E8


- 76,800 pixels (320 x 240)




## New Exclusive MSX Thermal Imaging Technology Made Affordable for Everyday Use

What is MSX?

Multi-Spectral Dynamic Imaging (MSX) for easier interpretation of an image - adds visible spectrum definition to IR images by detecting the edges of objects and including that detail in the thermal image. Text becomes clearly visible so that you can read a label or identifier within the IR image. This exclusive function provides extraordinary thermal detail that instantly highlights and orients problem locations and eliminates the need to refer back to a visual image for detail.



Panel without MSX



Panel with MSX

## Imaging Specifications

| FEATURES                | FLIR E4                    | FLIR E5                                       | FLIR E6                                       | FLIR E8                                       |
|-------------------------|----------------------------|-----------------------------------------------|-----------------------------------------------|-----------------------------------------------|
| IR Pixel Resolution     | 4,800 (80 x 60)            | 10,800 (120 x 90)                             | 19,200 (160 x 120)                            | 76,800 (320 x 240)                            |
| Thermal Sensitivity     | <0.15°C                    | <0.10°C                                       | <0.06°C                                       | <0.06°C                                       |
| Temperature Range       | -4 to 482°F (-20 to 250°C) |                                               |                                               |                                               |
| Measurement modes       | Centerspot                 | Centerspot, Area Box, Auto Hot/Cold detection | Centerspot, Area Box, Auto Hot/Cold detection | Centerspot, Area Box, Auto Hot/Cold detection |
| Frame Rate              | 9Hz                        |                                               |                                               |                                               |
| Field of View           | 45° x 34°                  |                                               |                                               |                                               |
| Focus                   | Focus free                 |                                               |                                               |                                               |
| Auto Hot/Cold Detection | No                         | Auto min/max markers within area              | Auto min/max markers within area              | Auto min/max markers within area              |

## Ordering Information

63901-0101 ..... FLIR E4 Compact Thermal Imaging Infrared Camera with MSX® Enhancement (80x60)  
 63901-0101-NIST ..... FLIR E4 with Certificate Traceable to NIST  
 63905-0501 ..... FLIR E5 Compact Thermal Imaging Infrared Camera with MSX® Enhancement (120x90)  
 63905-0501-NIST ..... FLIR E5 with Certificate Traceable to NIST  
 63902-0202 ..... FLIR E6 Compact Thermal Imaging Infrared Camera with MSX® Enhancement (160x120)  
 63902-0202-NIST ..... FLIR E6 with Certificate Traceable to NIST  
 63903-0303 ..... FLIR E8 Compact Thermal Imaging Infrared Camera with MSX® Enhancement (320x240)  
 63903-0303-NIST ..... FLIR E8 with Certificate Traceable to NIST

### ACCESSORIES

T198529 ..... Pouch  
 T198530 ..... Replacement battery  
 T198531 ..... External battery charger  
 T198532 ..... Car Charger  
 T198534 ..... Power supply/charger with EU, UK, US and AU plugs  
 T198533 ..... USB cable  
 T198528 ..... Hard Transport Case



10-Year Detector  
 Protection  
 5-Year Battery  
 2-Year Parts & Labor



BOSTON

FLIR Systems, Inc.  
 PH: +1 866.477.3687  
 PH: +1 978.901.8000

PORTLAND  
 Corporate Headquarters  
 FLIR Systems, Inc.  
 PH: +1 866.477.3687

CANADA  
 FLIR Systems, Ltd.  
 PH: +1 800.613.0507

MEXICO/LATIN AMERICA  
 FLIR Systems Brasil  
 Av. Antonio Bardella  
 PH: +55 15 3238 8070

Equipment described herein may require US Government authorization for export purposes. Diversion contrary to US law is prohibited. The images displayed may not be representative of the actual resolution of the camera shown. Specifications are subject to change without notice. ©2013 FLIR Systems, Inc. All rights reserved. 3723 (Rev. 09/13)

www.flir.com  
 NASDAQ: FLIR