

UL STYLE 1007/1569

ALLIED PART NO.	AWG SIZE	CONDUCTOR STRANDING	NOMINAL O.D.	APPROX. LBS./MFT
07-28-1T	28	Solid	.045	1.41
07-28-7T	28	7/36	.047	1.44
07-26-1T	26	Solid	.048	1.83
07-26-7T	26	7/34	.051	1.94
07-24-1T	24	Solid	.052	2.62
07-24-7T	24	7/32	.057	2.76
07-22-1T	22	Solid	.059	3.64
07-22-7T	22	7/30	.064	3.87
07-20-1T	20	Solid	.065	4.99
07-20-10T	20	10/30	.071	5.00
07-18-1T	18	Solid	.074	7.22
07-18-16T	18	16/30	.081	7.26
07-16-1T	16	Solid	.084	10.26
07-16-26T	16	26/30	.094	10.86
69-14-41T	14	41/30	.110	16.24
69-12-65T	12	65/30	.131	24.83
69-10-105T	10	105/30	.145	36.51

UL STYLE 1015

ALLIED PART NO.	AWG SIZE	CONDUCTOR STRANDING	NOMINAL O.D.	APPROX. LBS./MFT
15-26-1T	26	Solid	.080	3.91
15-26-7T	26	7/34	.083	4.00
15-24-1T	24	Solid	.084	4.97
15-24-7T	24	7/32	.089	5.11
15-22-1T	22	Solid	.090	6.04
15-22-7T	22	7/30	.095	6.27
15-20-1T	20	Solid	.092	7.59
15-20-10T	20	10/30	.102	7.60
15-18-1T	18	Solid	.106	10.10
15-18-16T	18	16/30	.112	10.16
15-16-1T	16	Solid	.115	14.12
15-16-26T	16	26/30	.125	14.36
15-14-1T	14	Solid	.128	19.83
15-14-41T	14	41/30	.140	20.10
15-12-1T	12	Solid	.145	29.23
15-12-65T	12	65/30	.163	29.66
15-10-1T	10	Solid	.165	41.70
15-10-105T	10	105/30	.175	42.20

UL STYLE 1061

ALLIED PART NO.	AWG SIZE	CONDUCTOR STRANDING	NOMINAL O.D.	APPROX. LBS./MFT
61-30-1T	30	Solid	.030	.75
61-28-1T	28	Solid	.033	.94
61-28-7T	28	7/36	.035	.94
61-26-1T	26	Solid	.038	1.31
61-26-7T	26	7/34	.039	1.40
61-24-1T	24	Solid	.042	1.92
61-24-7T	24	7/32	.045	2.06
61-22-1T	22	Solid	.047	2.84
61-22-7T	22	7/30	.051	3.07
61-20-1T	20	Solid	.053	4.22
61-20-10T	20	10/30	.057	4.23
61-18-1T	18	Solid	.061	6.32
61-18-16T	18	16/30	.066	6.36
61-16-1T	16	Solid	.072	9.52
61-16-26T	16	26/30	.081	9.76

Above items can be striped, twisted, cut & stripped. Center conductor is available as solid, tinned overcoat, prebond or bare copper.

International Headquarters: 101 Kestrel Drive Collegeville, PA 19426 P: 800-828-9473 P: 484-928-6700 F: 484-928-6720

New Hampshire

P: 800-227-1025
F: 603-423-9391

Florida

P: 407-869-7004
F: 407-869-7006

South Carolina

P: 866-510-7924
F: 864-289-9645

Tennessee

P: 888-860-6149
F: 615-355-9664

Wisconsin

P: 800-535-3271
F: 800-546-5563

HOOK-UP WIRE

UL 1007/1569

UL and CSA Dual Rated Wire
UL Style 1007 300 V 80°C
UL Style 1569 300 V 105°C
CSA Type TR-64 300 V 90°C
Passes UL VW-1 Flame Test

Description:

Stranded Tinned Copper, Color Coded
Polyvinylchloride Insulation, .016 nominal
Insulation Thickness

Characteristics:

- Temperature Range: -40°C to +105°C
- Voltage Rating: 300 volts

UL 1015

UL and CSA Style TEW, MTW
UL Style 1015 600 V 105°C
UL Style 1032 1000 V 90°C
UL Style 1230 600 V 105°C dry; 60°C Wet
Marine approvals for 16-8 AWG: UL Standard
1426 BC-5W2, SAEJ378, USCG, ABYC, and NMNA
Passes UL VW-1 Flame Test

Description:

Stranded Tinned Copper, Color Coded
Polyvinylchloride Insulation, .032 nominal
Insulation Thickness

Characteristics:

- Temperature Range: -40°C to +105°C
- Voltage Rating: 600 volts

UL 1061

UL and CSA Dual Rated Wire
UL Style 1061 300 V 80°C
CSA Type SR-PVC
Passes UL VW-1 Flame Test

Description:

Stranded Tinned Copper, Color Coded
Semi-Rigid Polyvinylchloride Insulation
.009 nominal wall

Characteristics:

- Temperature Range: -10°C to +80°C
- Voltage Rating: 300 volts