





Technical drawing of a mechanical part showing dimensions and tolerances.

Dimensions:

- .008 X .018 TAIL [0.20] [0.46]
- .075 [1.90]
- .235 [5.97]
- .205 [5.21] OUTSIDE ROW
- .305 [7.75]
- .275 [6.99] INSIDE ROWS

Feature:

- 6 (Feature Number)



- | | |
|--------------|----------|
| 180 & 91 | 446447-1 |
| CAVITY IDENT | PART NO |

4805 (1/15)