



260-8[®] & 260-8P[®] Analog VOM

When a Digital Multimeter won't do the Job

Professionals have long recognized that a Simpson 260 analog meter is superior to the best DMM when monitoring fluctuating trends and rates.

The 260-8 features more attributes than its predecessors. Standard and high-energy fusing in conjunction with diode network meter movement protection makes the 260-8 the best combination of quality and affordability.

The 260-8P has an additional relay overload protection circuit that is resettable and also provides audible continuity checking.

- **36 Measurement Ranges** - Covers both AC and DC Voltage and Current measurements, as well as resistance testing
- **Connections Safeguarded** - Standard size reverse/recessed safety jacks prevent operator and/or tool contact with electrical connections of the instrument
- **Overload Protection** - Diode network protects instrument from overload damage during use (260-8P and 260-8PRT only)
- **Rugged Construction** - The Phenolic case is designed with heavy reinforced walls for maximum durability; self-shielding taut-band provides added shock resistance for the meter movement
- **Portable, for the Workshop, Lab, or in the Field** - Portable enough to carry, with benchtop accuracy
- **Versatile** - Full-size test leads with threaded probe tips for screw-on alligator clips. Eliminates the need to change test leads while working
- **Simple Operation** - Two knobs control the selection of ranges and functions



Specifications (Continued)

AC CURRENT

Ranges: Up to 250 amperes with AC Amp-Clamp Adapter Accessory #00545

DECIBEL

5 Ranges: -20 to +50dB

Reference: 0dB= 1mW into 600Ω

DC CURRENT

Ranges	Accuracy	Voltage Drop: (Nominal)
50 μA, 1mA, 10mA, 100mA, 500mA, 10A	1.5% full scale 50 μA 2.0% of full scale, all others	250mV on 50 μA/1mA; 255mV on 10mA/10A; 300mV on 100mA; 500mV on 500mA

RESISTANCE

Ranges	Accuracy	Max. Indication
Rx 1 Rx 100 Rx 10K	2.5° of arc Rx 1 2.0° of arc on all others	0-2KΩ 0-200KΩ 0-20MΩ

RATED CIRCUIT-TO-GROUND VOLTAGE: 1000V (AC or DC) max.

FUSE: F1 1A, 250V, type 3AG, quick acting Littelfuse[®] Type 312001; F2 2A, 600V Littelfuse[®] Type BLS or 2A 600V, Bussman[®] Type BBS.

BATTERIES: 1.5V D, 9V (Neda No. 13F, 1604A)

PHYSICAL: Dimensions 7"(H)x5.5"(W) x 3.1"(D), (18x14x8cm)

Weight 3 lbs. (1.4Kg)

Specifications subject to change without notice.

Specifications

DC VOLTAGE

Ranges	Accuracy	Sensitivity
250mV, 1V, 2.5V, 10V, 25V, 50V, 250V, 500V, 1000V	2% of full scale	20KΩ per volt

AC VOLTAGE

Ranges	Accuracy	Sensitivity
2.5V, 10V, 25V, 50V, 250V, 500V, 1000V	3% of full scale	5KΩ per volt

Ordering Information

ANALOG MULTIMETERS	Catalog No.	ACCESSORIES	Catalog No.	ACCESSORIES	Catalog No.
260-8, General Purpose	12388	Model 150-2 Amp-Clamp Adapter	00545	Roll-Top Case	00248
260-8P, Relay Protected	12391	Probe Set, threaded w/clips	00043	Case, Hard Leatherette Front Load	00805
260-8RT, Roll Top Case	12389	Case, Yellow Padded Polyester	00832	Case, Molded Plastic	45028
260-8PRT, Protected, Roll Top Case	12392	Case, Black Padded Polyester	00834		

Additional accessories on pages 22-24.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Simpson:

[12389](#) [12388](#) [12392](#) [12391](#) [12388-NIST W/DATA](#)