

PTV09 Series - 9 mm Potentiometer

Taper..... Linear, audio
Standard Resistance Range
..... 1 K ohms to 1 M ohms
Standard Resistance Tolerance..... $\pm 20\%$
Residual Resistance
..... 500 ohms or $\pm 1\%$ max.

Operating Temperature.....-10 °C to +50 °C
Power Rating
(Linear and Audio).....0.05 watt
Maximum Operating Voltage
(Linear and Audio)..... 20 VDC, 50 VAC
Sliding Noise 100 mV max.

Mechanical Angle $280^{\circ} \pm 10^{\circ}$
Rotational Torque 10 to 100 g·cm
Detent Torque 20 to 200 gf·cm
Stop Strength 2 kg·cm min.
Rotational Life 10,000 cycles
Soldering Condition
..... 300°C max. within 3 seconds
Hardware One flat washer and one
hex nut supplied with bushing version

PTV09A - 2 0 20 F - B 203

Model _____

Terminal Configuration _____

(Pin Layout)

- 1 = Horizontal/Rear Mount
w/Sleeve Bushing
- 2 = Vertical/Side Mount,
Bushingleess,
10 mm Height
- 3 = Vertical/Side Mount,
Bushingleess,
6.5 mm Height
- 4 = Horizontal/Rear Mount,
Bushingleess
- 5 = Horizontal/Rear Mount
w/Plastic Plain Bushing
- 6 = Horizontal/Rear Mount
w/Metal Threaded
Bushing
- 7 = Vertical/Side Mount
w/Sleeve Bushing,
6.5 mm Height
- 8 = Vertical/Side Mount
w/Sleeve Bushing,
10 mm height

Option _____

0 = No Detent 2 = Center

Standard Shaft Length _____

15 = 15 mm**	25 = 25 mm
20 = 20 mm	30 = 30 mm

Shaft Style _____

F = Flat Type Insulated Shaft
S = Insulated Knurled (18 Teeth)
U = Insulated Knurled (40 Teeth)


Resistance Taper _____

Taper Series followed by Curve


Resistance Code (See Table) _____

Other styles available.
** Bushingleess version only.

PTV09A-1
(Horizontal/Rear Mount w/Sleeve Bushing)





RECOMMENDED PCB LAYOUT (HORIZONTAL/REAR MOUNT)



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

PTV09A-2
(Vertical/Side Mount,
Bushingleless, 10 mm Height)

RECOMMENDED PCB LAYOUT
(VERTICAL/SIDE MOUNT)

Standard Resistance Table

Resistance (Ohms)	Resistance Code
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104
200,000	204
500,000	504
1,000,000	105

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

Applications


- Commercial communications equipment
- Portable electronics
- Amplifiers/mixers/drum machines/synthesizers
- Consumer goods
- Commercial appliances

PTV09 Series - 9 mm Potentiometer


BOURNS®

Product Dimensions (Continued)


PTV09A-3
(Vertical/Side Mount,
Bushings, 6.5 mm Height)



PTV09A-4
(Horizontal/Rear Mount, Bushingless)




PTV09A-5
(Horizontal/Rear Mount
w/Plastic Plain Bushing)




Shaft Styles

F-Type




L	15 (.591)	20 (.787)	25 (.984)	30 (1.181)
F	6 (.236)	7 (.275)	12 (.472)	12 (.472)

S-Type



L	15 (.591)	20 (.787)	25 (.984)	30 (1.181)
A	7 (.275)	7 (.275)	7 (.275)	7 (.275)

U-Type



L	15 (.591)	20 (.787)	25 (.984)	30 (1.181)
A	6 (.236)	7 (.275)	7 (.275)	7 (.275)


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications. Specifications are subject to change without notice.

PTV09 Series - 9 mm Potentiometer

BOURNS®


Product Dimensions (Continued)

PTV09A-6
(Horizontal/Rear Mount
w/Metal Threaded Bushing)




SHAFT SHOWN IN CENTER POSITION

PTV09A-7
(Vertical/Side Mount
w/Sleeve Bushing, 6.5 mm Height)




DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

PTV09A-8
(Vertical/Side Mount
w/Sleeve Bushing, 10 mm Height)



Mounting Hardware




Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.




PTV09 Series - 9 mm Potentiometer

BOURNS®

Derating Curve



Tapers



BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

Europe: Tel: +41-41 768 5555 • Fax: +41-41 768 5510

The Americas: Tel: +1-951 781-5500 • Fax: +1-951 781-5700

www.bourns.com

REV. 08/13

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.