


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	—	INITIAL RELEASE



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135101-02-06.00	6.00
135101-02-12.00	12.00
135101-02-24.00	24.00
135101-02-36.00	36.00

- NOTE:
1. PERFORM CONTINUITY AND HI-POT TESTING.
 2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

3	009-954-341	HEAT SHRINK TUBING, BLACK, 3/16" DIAMETER	A/R FT
2	009-881-159	COAXIAL CABLE, RG174/U	A/R FT
1	132114	CONNECTOR, SMA STRAIGHT PLUG, GOLD	2
	PN	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE	Amphenol Connex			
DRAWN	G.R.S.	02/03/09				
CHECKED			PART DESCRIPTION			
ISSUED			SMA PLUG TO SMA PLUG, RG174			
SHEET	1 OF 1		PART NO.			
			135101-02-XX.XX			
CAD FILE			DWG. NO.	135101-02-XX.XX.DWG	REV. NC	SIZE A
			SCALE NA			