



Circuit Diagram



DIMENSIONS: in.

Specifications:

- Type: AC to DC (standard)
- Primary voltage: 117VAC 60Hz
- Primary exciting current: 35mA max.
- Secondary voltage (no load): 11.5VDC $\pm 5\%$
- Secondary voltage (full load): 9VDC $\pm 5\%$
- Rated secondary current: DC 200mA 60Hz
- Temperature rise: $< 45^{\circ}\text{C}$
- Breakdown voltage (hi-pot): 1500VAC 60Hz for 1 minute
- Insulation (coil~coil): 100M Ω (1 minute) 500VDC
- Core: EI-41, hilite core H-23 0.5mm
- Inner & outer wrap insulation: polyester tape
- Bobbin: nylon 66
- Impregnation: varnish
- Lead wire: 60mm length, 24AWG
- Cabinet: ABS materials
- Capacitor: 470mfd x 16V
- Rectifier: IN4001 (2 pieces)
- DC plug: 3.5mm male plug with 6 ft. of cable
- AC plug: flat pins
- Length: 14.5mm ± 0.5 mm
- Polarity: positive tip polarity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41AC114