




PART NO.	ENG. NO.
02-09-1205	4550-A(P901)
02-09-1206	4550-A(P901)L
02-09-5169	4550-A(P558)
02-09-5170	4550-A(P558)L



SECTION "A-A"

SECTION "B-B"





LEGEND

4550-A(****)*

P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE



CHAIN FORM
FULL SCALE

NOTES:

1. MATERIAL: PHOSPHOR BRONZE
2. FINISHES:
901 - HOT TIN DIP .000020/(0.00051) MIN.
558 - SELECT GOLD PLATE .000030/(0.00076) MIN. IN CONTACT AREA, OVER .000050/(0.00127) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH.
3. THIS PART CONFORMS TO PROD. SPEC. 02-09.
4. TERMINAL FOR USE WITH .093/(2.36) SERIES HOUSINGS AND WILL ACCEPT 14 THRU 20 AWG WIRE.
5. INSERTION FORCE: 3.5 LBS. MAX. WHEN TERMINAL IS INSERTED INTO AN .093 SERIES HOUSING.
6. RETENTION: 20 LBS. MIN. FROM HOUSING.

REMOVE DIMPLE EC NO: UCP2015-0104 DRWN:JDFX 2014/07/29 CHKD:MK/PPER 2014/07/29 APPR:FSM/TH 2014/07/31	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 6:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY GWC	DATE 1991/05/02	TITLE CRIMP TERMINAL, FEMALE			
			4 PLACES ± ---	± ---	CHECKED BY RW	DATE 1991/05/02				
			3 PLACES ± ---	± .010	APPROVED BY GWF	DATE 1991/05/02	molex			
			2 PLACES ± 0.25	± .014	MATERIAL NO. SEE CHART				DOCUMENT NO. SD-4550-*	
1 PLACE ± 0.35	± ---	SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1				
0 PLACE ±	±	ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						