


|                        |                                      |
|------------------------|--------------------------------------|
| <b>DRAWING NUMBER:</b> | <b>10-201-X-XX</b>                   |
| <b>PRODUCT GROUP:</b>  | TERMINALS                            |
| <b>SUB-GROUP:</b>      | COMMERCIAL NON-INSULATED TERMINALS   |
| <b>DESCRIPTION:</b>    | NON-INSULATED DOUBLE TURRET TERMINAL |



| BOARD / PANEL MOUNTING METHOD | MOUNTING HOLE SIZE | DRILL SIZE | FEED THRU COMBINATION |
|-------------------------------|--------------------|------------|-----------------------|
| SWAGE MOUNT                   | 0.076" ± 0.001     | #48        | N/A                   |

## PART NO. STRUCTURE:

|             |   |           |   |        |
|-------------|---|-----------|---|--------|
| 10-201      | - | X         | - | XX     |
| PART SERIES |   | DIMENSION |   | FINISH |

## MATERIAL OPTIONS:

**10-201**-X-XX

| COMPONENT | MATERIAL | MATERIAL AND SPECIFICATION                 |
|-----------|----------|--------------------------------------------|
| TERMINAL  | BRASS    | BRASS PER ASTM B16, ALLOY C36000, 1/2 HARD |

## DIMENSION OPTIONS:

10-201-**X**-XX

| DIMENSION | A   | D   | PIN DIAMETER | OVERALL LENGTH | SHANK LENGTH (L) | BOARD/PANEL THICKNESS |
|-----------|-----|-----|--------------|----------------|------------------|-----------------------|
| 1         | N/A | N/A | N/A          | 0.237"         | 0.051"           | 1/32"                 |
| 2         | N/A | N/A | N/A          | 0.268"         | 0.082"           | 1/16"                 |
| 3         | N/A | N/A | N/A          | 0.299"         | 0.113"           | 3/32"                 |
| 4         | N/A | N/A | N/A          | 0.331"         | 0.145"           | 1/8"                  |
| 6         | N/A | N/A | N/A          | 0.393"         | 0.207"           | 3/16"                 |
| 8         | N/A | N/A | N/A          | 0.456"         | 0.270"           | 1/4"                  |

## FINISH - PLATING OPTIONS:

10-201-X-XX

| FINISH CODE | COMPONENT | FINISH             | FINISH AND SPECIFICATION                                                                            |
|-------------|-----------|--------------------|-----------------------------------------------------------------------------------------------------|
| 01          | TERMINAL  | SILVER             | 0.000300"MIN. SILVER PER ASTM B700, TYPE 2, GRADE D WITH A NON-CHROMATE PRESERVATIVE TREATMENT      |
| 03          | TERMINAL  | GOLD               | 0.000010"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000050"MIN. NICKEL PER SAE-AMS-QQ-N-290    |
| 035         | TERMINAL  | GOLD               | 0.000050"MIN. GOLD PER ASTM B488, TYPE II, CODE C OVER 0.000050"MIN. NICKEL PER SAE-AMS-QQ-N-290    |
| 04          | TERMINAL  | ELECTRO-TIN        | 0.000300"MIN. ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418                  |
| 044         | TERMINAL  | BRIGHT ELECTRO-TIN | 0.000300"MIN. BRIGHT ELECTRO-TIN PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418           |
| 05          | TERMINAL  | ELECTRO-SOLDER     | 0.000300"MIN. ELECTRO-SOLDER PER SAE-AMS-P-81728 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418         |
| 088         | TERMINAL  | BRIGHT TIN-LEAD    | 0.000300"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418 |

## TOLERANCES:\*

| DECIMAL | FRACTIONAL | ANGULAR | DRAWING ORIGATION DATE | LAST MODIFICATION DATE |
|---------|------------|---------|------------------------|------------------------|
| ± 0.005 | ± 1/64     | ± 5 °   | 11/20/2000             | 3/1/2017               |

\*All dimensions are in inches.

## RoHS COMPLIANCE:

## 10-201-1-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-1-01  | YES            |
| 10-201-1-03  | YES            |
| 10-201-1-035 | YES            |
| 10-201-1-04  | YES            |
| 10-201-1-044 | YES            |
| 10-201-1-05  | NO             |
| 10-201-1-088 | NO             |

## 10-201-2-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-2-01  | YES            |
| 10-201-2-03  | YES            |
| 10-201-2-035 | YES            |
| 10-201-2-04  | YES            |
| 10-201-2-044 | YES            |
| 10-201-2-05  | NO             |
| 10-201-2-088 | NO             |

## 10-201-3-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-3-01  | YES            |
| 10-201-3-03  | YES            |
| 10-201-3-035 | YES            |
| 10-201-3-04  | YES            |
| 10-201-3-044 | YES            |
| 10-201-3-05  | NO             |
| 10-201-3-088 | NO             |

Continued on next page...

## RoHS COMPLIANCE CONTINUED:

## 10-201-4-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-4-01  | YES            |
| 10-201-4-03  | YES            |
| 10-201-4-035 | YES            |
| 10-201-4-04  | YES            |
| 10-201-4-044 | YES            |
| 10-201-4-05  | NO             |
| 10-201-4-088 | NO             |

## 10-201-6-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-6-01  | YES            |
| 10-201-6-03  | YES            |
| 10-201-6-035 | YES            |
| 10-201-6-04  | YES            |
| 10-201-6-044 | YES            |
| 10-201-6-05  | NO             |
| 10-201-6-088 | NO             |

## 10-201-8-XX

| PART NUMBER  | RoHS COMPLIANT |
|--------------|----------------|
| 10-201-8-01  | YES            |
| 10-201-8-03  | YES            |
| 10-201-8-035 | YES            |
| 10-201-8-04  | YES            |
| 10-201-8-044 | YES            |
| 10-201-8-05  | NO             |
| 10-201-8-088 | NO             |

## TOOLING:

| INSTALLATION TOOL:<br>ARBOR PRESS | INSTALLATION TOOL:<br>ANVIL<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>PRESS-FIT / ROLL SWAGE / RIVET PUNCH<br>(ARBOR PRESS OPERATED) | INSTALLATION TOOL:<br>FLARE SWAGE PUNCH<br>(ARBOR PRESS OPERATED) |
|-----------------------------------|-------------------------------------------------------|--------------------------------------------------------------------------------------|-------------------------------------------------------------------|
| TM1                               | TA94-50-20                                            | TP10-201                                                                             | N/A                                                               |

## NOTES:

| DATASHEET NOTES                                                                                                                                             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N/A                                                                                                                                                         |
| INSTRUCTION NOTES                                                                                                                                           |
| SEE GENERAL SWAGING INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE <a href="http://WWW.CONCORD-ELECTRONICS.COM">WWW.CONCORD-ELECTRONICS.COM</a> . |