

## Plug-in connector - CIOC 4-20-1,2-FL - 1701294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 3 A, Rated voltage (III/2): 32 V, Number of positions: 4, Pitch: 2 mm, Connection method: Insulation displacement connection QUICKON, Color: green, Contact surface: Gold

### Product Features

- ✓ Conductor connection using standard pliers
- ✓ Connection of AWG conductors with 7-strand conductor structure and PVC insulation, other conductor types can be used on request
- ✓ Additional CIOC 3-2...-FL versions available on request
- ✓ Quick and reliable connection thanks to displacement connection
- ✓ Colored, transparent hoods for checking correct contacting of the displacement connection
- ✓ Gold-plated contact system
- ✓ Panel feed-through with CIOC ...-FL
- ✓ For sensor/actuator wiring



### Key commercial data

|                      |                                                                                                         |
|----------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit         | 1 PCE                                                                                                   |
| GTIN                 | <br>4 046356 030434 |
| Custom tariff number | 85366990                                                                                                |
| Country of origin    | JAPAN                                                                                                   |

### Technical data

#### Dimensions / positions

|                     |      |
|---------------------|------|
| Pitch               | 2 mm |
| Dimension a         | 6 mm |
| Number of positions | 4    |

#### Technical data

|                   |         |
|-------------------|---------|
| Range of articles | CIOC-FL |
|-------------------|---------|

## Plug-in connector - CIOC 4-20-1,2-FL - 1701294

### Technical data

#### Technical data

|                                         |                     |
|-----------------------------------------|---------------------|
| Rated voltage (III/2)                   | 32 V                |
| Connection in acc. with standard        | EN-VDE              |
| Nominal current $I_N$                   | 3 A                 |
| Nominal cross section                   | 0.5 mm <sup>2</sup> |
| Maximum load current                    | 3 A                 |
| Insulating material                     | PBT/PC              |
| Inflammability class according to UL 94 | V0                  |

#### Connection data

|                                        |                      |
|----------------------------------------|----------------------|
| Conductor cross section stranded min.  | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded max.  | 0.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min. | 22                   |

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002638 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260705 |
| eCl@ss 7.0 | 27440309 |

### Approvals

#### Approvals

## Plug-in connector - CIOC 4-20-1,2-FL - 1701294

### Approvals

#### Approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized

#### Ex Approvals

#### Approvals submitted

#### Approval details

|                                                                                                 |       |
|-------------------------------------------------------------------------------------------------|-------|
| UL Recognized  |       |
|                                                                                                 |       |
| mm²/AWG/kcmil                                                                                   | 26-20 |
| Nominal current I <sub>N</sub>                                                                  | 3 A   |
| Nominal voltage U <sub>N</sub>                                                                  | 32 V  |

|                                                                                                    |       |
|----------------------------------------------------------------------------------------------------|-------|
| cUL Recognized  |       |
|                                                                                                    |       |
| mm²/AWG/kcmil                                                                                      | 26-20 |
| Nominal current I <sub>N</sub>                                                                     | 3 A   |
| Nominal voltage U <sub>N</sub>                                                                     | 32 V  |

|                                                                                          |  |
|------------------------------------------------------------------------------------------|--|
| GOST  |  |
|                                                                                          |  |


|                                                                                          |  |
|------------------------------------------------------------------------------------------|--|
| GOST  |  |
|                                                                                          |  |

|                                                                                                      |  |
|------------------------------------------------------------------------------------------------------|--|
| cULus Recognized  |  |
|                                                                                                      |  |


## Plug-in connector - CIOC 4-20-1,2-FL - 1701294

### Drawings

Dimensioned drawing




Dimensioned drawing



$a=6.5$

Dimensioned drawing



$a=6.5$