

## RoHS Compliance Material Declaration Report

Company:	Pericom
Name:	Nang Su
Title:	Quality Engineer
e-mail:	<a href="mailto:nsu@pericom.com">nsu@pericom.com</a>

Address:	3545 North First Street, San Jose, CA, 95134
Phone number:	(408) 435 0800
Date:	3/14/2007

**Part Detail**

Pericom Part Number	Manufacturer part description	Package Type	Number of Pin/Terminal	Component overall weight
PS393ESEE	Quad SPST 17V Analog Switch	SOIC (150mil width)	16	0.14615

**RoHS Compliance**

Is Part compliant to EU RoHS Directive? [1] Yes, [2] Yes with tech exemption* [3] Yes but needs product application exemption* [4] No	RoHS tech exemption [2] details.	Date Component was RoHS Compliant.
Yes	N/A	Since Inception

**Content of RoHS restricted materials (g)**

Lead	Cadmium	Mercury	Hexavalent Chromium	Polybrominated biphenyls (PBB)	Polybrominated Diphenylethers (PBDE)	RoHS restricted substance added intentionally? For what reason?
0	0	0	0	0	0	N/A

**Component Soldering Process**

Interconnect Composition, (Metallurgy of the lead/terminal)	JEDEC JEDS97 Pb-free Category	Compatible with a 260C 10s Pb-Free assembly process	Backward compatible with SnPb assembly	Maximum Processing Temperature (°C)	Max Temperature Duration	Max Number of reflow cycles
Sn	e3	Yes	Yes	260	40	3

**Plastics (if applicable)**

Oxygen Index	Type of plastic material used in the component	Fire: UL Rating	MSL Level (per JEDEC STD 020C)
>28%	Epoxy Resin	V-0	1

**Tin (Sn) Plating (If Applicable)**

Tin (Sn) Plating – is it Matte (M) or Bright (B)?	Tin (Sn) Plating Thickness	Tin (Sn) plating is there a Nickel (Ni) Barrier? - Yes / No	Nickel Barrier Thickness	If no Nickel barrier is the tin (Sn) termination finish heat treated?	Performed Tin Whisker Test ?
M	7 to 20 $\mu$ m	No	N/A	Yes, 150C / 1 Hr	Yes

**Bismuth (Bi)**

Bismuth (Bi) Content (if applicable)
0