




DESCRIPTION: R/A .370 FOOTPRINT MACHINED MALE



	A	B	C	E	F	G
9	1.213 30.81	.984 24.99	.494 12.55	.035 0.89	.235 5.97	0.436 11.07
15	1.541 39.14	1.312 33.32	.494 12.55	.035 0.89	.235 5.97	0.763 19.38
25	2.088 53.04	1.852 47.04	.494 12.55	.035 0.89	.230 5.84	1.308 33.22
37	2.729 69.32	2.500 63.50	.494 12.55	.035 0.89	.230 5.84	1.962 49.83
50	2.635 66.92	2.406 61.11	.605 15.37	.035 0.89	.230 5.84	1.744 44.32




SPECIFICATIONS:
MATERIALS:
SHELL: STEEL, YELLOW CHROMATE OR TIN PLATED
INSULATOR: UL 94V-0 RATED WHITE PBT
+30% FIBER-GLASS OR NYLON-66
ELECTRICALS:
CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOHMS MAX
INSULATOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: WAYNE ROBBINS		DATE: 9-01-98	
			CHECKED:		DATE:	
	NorComp		SCALE: 1:1		SHEET OF	
		DWG NO. 174-EXX-11X-001		REV 6		

DESCRIPTION:

173/174 SERIES



175/176 SERIES



MATERIAL:
COLD ROLLED STEEL

PLATING:
CLEAR ZINC OR YELLOW CHROMATE

HARDWARE OPTIONS

REPLACE -XX IN LAST 3 DIGITS WITH OPTION CHOSEN

173/174 SERIES

14X = SHORT BRACKET & 4-40 FEMALE HEX SOCKET
24X = SHORT BRACKET & 4-40 SCREW

175/176 SERIES

15X = LONG BRACKET & 4-40 FEMALE HEX SOCKET
25X = LONG BRACKET & 4-40 SCREW

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS	DATE: 2-20-02
			CHECKED:	DATE:
NorComp		SCALE:	SHEET 1 OF 1	REV 1
		DWG NO. R/A BRACKET OPTIONS FOR MACHINED CONTACTS		