




Electrical Characteristics

Nominal Impedance:	75 ohms
Frequency Range:	DC to 2 GHz
VSWR:	1.35:1 maximum
Operating Voltage (rms):	250 V maximum at sea level

Mechanical Characteristics

Mating Cycles:	200 cycles minimum
----------------	--------------------

Environmental Characteristics

Temperature Range:	-65 °C to +165 °C
--------------------	-------------------

PART	DESCRIPTION
1 Body	Brass, nickel plated
2 Contact	Brass, nickel plated
3 Dielectric	PTFE

CAD Issue	SN	2	26 Feb 03
First Issue	SN	1	25 Nov 94
DESCRIPTION OF REVISION	APPVD	ISS	DATE

For stripping and assembly instructions see Drawing Number: VAIF1101



Connectivity Division

Station Road, Bordon,
Hampshire, GU35 0LG, England
Tel: +44 (0)1420 488661
Fax: +44 (0)1420 488014

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:
± 0.2mm unless
otherwise stated

DRAWN BY:

S Nash

CHECKED BY:

APPROVED BY:

DATE:

26 Feb 03

TITLE:

F Crimp Plug for RA519,
CT167 and RG11

PART NUMBER:

VF10-519

PAGE: 1 of 1