




- 1

APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 2

BODY MATERIAL THK 1.016±0.051 [.040±.002]
- 3

105°C[221°F] MAX OPERATING TEMPERATURE
- 4

300 VOLT MAX.
- 5

CIRCULAR MIN AREA: 2.62–6.64 mm² [5180–13100] SOLID OR STRANDED.
- 6

UL LISTED E13288 12–10 AWG SOLID OR STRANDED.
- 7

CSA CERTIFIED LR7189 12–10 AWG SOLID OR STRANDED.
- 8

MILITARY MS25036–157 CLASS 1.
- 9

MILITARY MS25036–157 CLASS 2.
- 10

MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B–152
INSULATION: NYLON PER ASTM D–4066, TYPE 1.
- 11

FINISH:
BODY & SLEEVE: TIN PLATE PER ASTM B–545
INSULATION: COLOR–YELLOW.
- 12

STAMP AMP  SEE TABLE, APPROX AS SHOWN.

2500	NONE	12–10	3.810–5.842 [.150–.230]	AMP 12–10*	"A"	ON TAPE	 2–320569–3
500	NONE	12–10	3.810–5.842 [.150–.230]	AMP 12–10*	"A"	LOOSE PIECE	  320569
QTY	COLOR STRIPE	WIRE SIZE	FOR WIRE INSULATION OD	STAMP	STYLE	PACKAGING	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL


TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± –

1 PLC ± –

2 PLC ± –

3 PLC ± 0.127[.005]

4 PLC ± –

ANGLES ± 0°30'

FINISH


DWN
RAGHAVENDRA
08SEP2008

CHK
T MICHIELUTTI
08SEP2008

APVD
T MICHIELUTTI
08SEP2008

PRODUCT SPEC
UL 486 A–B

APPLICATION SPEC
114–2157

WEIGHT
–

CUSTOMER DRAWING

 TE Connectivity

NAME
TERMINAL
RING TONGUE, NYLON, PIDG,
WIRE SIZE: 12–10 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=320569

RESTRICTED TO
–

SCALE
2:1

SHEET
1 OF 2

REV
U1

