

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FRODOPT, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

IHTI

(M)IHTI
ISSUE 9

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CATALOG LISTING

IHTI

PAGE 1 OF 1


M

DRAWING
NUMBER

ISSUE
19

REVISIONS

A	CO16180	RER	1 SEP 61
B	CO16367	RER	24 NOV 61
C	CO18487	LEB	26 SEPT 63
D	CO21919	OMW	12 APR 67
E	CO29241	RER	30 AUG 71
F	CO32050	RER	17 MAY 73
G	CO-36610	KSW	10 FEB 76
H	CO-53398	SL	21 JUN 83
J	CO-54474	DJS	3 FEB 84
K	CO-92890	CSL	6 MAY 98



NOTE-

- 1-SWITCH WILL WITHSTAND TEMPERATURE OF 1000°F MAX
- 2 RECOMMENDED APPLIED TORQUE FOR A 6-32 UNC STAINLESS STEEL TERMINAL IS 10 IN LB MAX. EXCEEDING THIS TORQUE COULD DAMAGE THE SWITCH

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 10-20 OZ

RELEASE FORCE — — — — — 6 OZ MIN

PRETRAVEL — — — — — .065 MAX

DIFFERENTIAL TRAVEL — — — — .010 MAX

OVERTRAVEL — — — — — .188 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L305 3A 1/10HP 125 VAC
2A 1/6HP 250 VAC



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT 2.4 OZ MAX

FORMTEK

DRAWN

CHECK

CHECK