


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- USED FOR:
 - 600V MAX VOLTAGE RATING
 - 257°F (125°C) MAX TEMP RATING (UL)
221°F (105°C) MAX TEMP RATING (CSA)
 - STRANDED COPPER WIRE ONLY
- WIRE STRIP LENGTH: $9/32 + 1/32$ [7.1 + .8]
- 0 - 0
- MAX WIRE INSULATION DIA .244 [6.20]
MIN WIRE INSULATION DIA .097 [2.46]
- MATERIAL:
 - STAMPING: NICKEL PLATED BRASS
 - HOUSING: TYPE 6/6 NYLON
- PACKAGING (CONTINUOUS MOLDED ON REEL):
 - BULK ONLY: -2K = 2000
- DIMENSIONS IN BRACKETS ARE IN mm OR mm2
- COLORS ARE TRANSLUCENT

PART NUMBER		TAB SIZE	WIRE RANGE AWG	HOUSING COLOR (NOTE 7)	DIMENSIONS			CA9 SERIES CRIMP DIE	CA-800 (EZ) SERIES CRIMP DIE
PREFIX	PK				A ±.02 [.5]	W ±.01 [.3]	B ±.01 [.3]		
DNF14250F1MX	-2K	.250 X .032 [6.3 X 0.8]	16-14* [1.5-2.5]	BLUE	.97 [24.6]	.41 [10.4]	.29 [7.4]	CD9-8B	CD-800-8
DNF18250F1MX	-2K	.250 X .032 [6.3 X 0.8]	22-18** [.5-1.0]	RED	.97 [24.6]	.41 [10.4]	.29 [7.4]		

PRESS/APPLICATOR COMPATIBILITY CHART

PRESS	CP-871	CP-861
APPLICATOR	CA9 CA-800EZ	CA-800

- * ALSO CSA CERTIFIED FOR USE WITH 2 #16 AWG OR 2 #18 AWG WIRES
 * ALSO CSA CERTIFIED FOR USE WITH 2 #18 AWG, 2 #20 AWG, OR 2 #22 AWG WIRES

							TITLE REELSMART DISCO MALE DISCONNECT FULLY INSULATED, EXPANDED NYLON .250 X .032, TAB SIZE CUSTOMER DRAWING					
							ITEM REVISION NAME N41545BA/05			PANDUIT		
							DATASET FILE NAME N41545BA/05					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XX ± .XXX ± ANGLES ± — THIRD ANGLE PROJECTION					
05	2/15	JHNU	TMR	RGB	ADDED PRESS/APPLICATOR COMPATIBILITY CHART REVISED TITLE BLOCK	N41545BA-DC	MATERIAL: SEE NOTES					
							DRAWING NUMBER: A41545					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY BDK	DATE	CHK RLS	SCALE	SHT 1 OF 1	SIZE A