

# EWSH-240

---



Universal Snap-in Hanger for elliptical waveguide 240

## Product Classification

<b>Product Type</b>	Hanger kit
---------------------	------------

## General Specifications

<b>Cable Type</b>	Elliptical waveguide
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in through hole

## Dimensions

<b>Height</b>	40.894 mm   1.61 in
<b>Width</b>	42.926 mm   1.69 in
<b>Length</b>	72.898 mm   2.87 in
<b>Waveguide Size</b>	WR42   WG20   R220

## Electrical Specifications

<b>Return Loss Effect</b>	0.1 dB
<b>DTF Effect</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

# EWSH-240

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Double cable weight

## Packaging and Weights

<b>Height, packed</b>	20 cm   7.874 in
<b>Width, packed</b>	20 cm   7.874 in
<b>Length, packed</b>	20 cm   7.874 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	1.6 kg   3.527 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

