



CY62128B

MoBL[®]

128K x 8 Static RAM

Features

- 4.5V – 5.5V operation
- CMOS for optimum speed/power
- Low active power (70 ns, LL version)
— 82.5 mW (max.) (15 mA)
- Low standby power (70 ns, LL version)
— 110 μ W (max.) (15 μ A)
- Automatic power-down when deselected
- TTL-compatible inputs and outputs
- Easy memory expansion with $\overline{CE_1}$, $\overline{CE_2}$, and $\overline{OE}$ options

Functional Description

The CY62128B is a high-performance CMOS static RAM organized as 131,072 words by 8 bits. Easy memory expansion is provided by an active LOW Chip Enable ($\overline{CE_1}$), an active HIGH Chip Enable ($\overline{CE_2}$), an active LOW Output Enable ($\overline{OE}$), and three-state drivers. This device has an

automatic power-down feature that reduces power consumption by more than 75% when deselected.


Writing to the device is accomplished by taking Chip Enable One ($\overline{CE_1}$) and Write Enable ($\overline{WE}$) inputs LOW and Chip Enable Two ($\overline{CE_2}$) input HIGH. Data on the eight I/O pins (I/O₀ through I/O₇) is then written into the location specified on the address pins (A₀ through A₁₆).

Reading from the device is accomplished by taking Chip Enable One ($\overline{CE_1}$) and Output Enable ($\overline{OE}$) LOW while forcing Write Enable ($\overline{WE}$) and Chip Enable Two ($\overline{CE_2}$) HIGH. Under these conditions, the contents of the memory location specified by the address pins will appear on the I/O pins.





The eight input/output pins (I/O₀ through I/O₇) are placed in a high-impedance state when the device is deselected ($\overline{CE_1}$ HIGH or $\overline{CE_2}$ LOW), the outputs are disabled ($\overline{OE}$ HIGH), or during a write operation ($\overline{CE_1}$ LOW, $\overline{CE_2}$ HIGH, and $\overline{WE}$ LOW).

The CY62128B is available in a standard 450-mil-wide SOIC, 32-pin TSOP type I and STSOP packages.

Logic Block Diagram



Pin Configurations



Selection Guide

			CY62128B-55	CY62128B-70	Unit
Maximum Access Time			55	70	ns
Maximum Operating Current (I_{CC})	Industrial	LL	20	15	mA
	Commercial	LL	20	15	mA
Maximum CMOS Standby Current (I_{SB2})	Industrial	LL	15	15	μ A
	Commercial	LL	15	15	μ A

Maximum Ratings

(Above which the useful life may be impaired. For user guidelines, not tested.)

Storage Temperature -65°C to $+150^{\circ}\text{C}$

Ambient Temperature with

Power Applied Power-up -55°C to $+125^{\circ}\text{C}$

Supply Voltage on V_{CC} to Relative GND^[1] -0.5V to $+7.0\text{V}$

DC Voltage Applied to Outputs

in High-Z State^[1] -0.5V to $V_{CC} + 0.5\text{V}$

DC Input Voltage^[1] -0.5V to $V_{CC} + 0.5\text{V}$

Current into Outputs (LOW) 20 mA

Static Discharge Voltage $> 2001\text{V}$
(per MIL-STD-883, Method 3015)

Latch-up Current $> 200\text{ mA}$

Operating Range

Range	Ambient Temperature ^[2]	V
Industrial	-40°C to $+85^{\circ}\text{C}$	$5\text{V} \pm 10\%$
Commercial	0°C to $+70^{\circ}\text{C}$	$5\text{V} \pm 10\%$

Electrical Characteristics Over the Operating Range

Parameter	Description	Test Conditions	62128B-55			62128B-70			Unit
			Min.	Typ. ^[3]	Max.	Min.	Typ. ^[3]	Max.	
V_{OH}	Output HIGH Voltage	$V_{CC} = \text{Min.}, I_{OH} = -1.0\text{ mA}$	2.4			2.4			V
V_{OL}	Output LOW Voltage	$V_{CC} = \text{Min.}, I_{OL} = 2.1\text{ mA}$			0.4			0.4	V
V_{IH}	Input HIGH Voltage		2.2		$V_{CC} + 0.3$	2.2		$V_{CC} + 0.3$	V
V_{IL}	Input LOW Voltage ^[1]		-0.3		0.8	-0.3		0.8	V
I_{IX}	Input Load Current	$\text{GND} \leq V_I \leq V_{CC}$	-1		$+1$	-1		$+1$	μ A
I_{OZ}	Output Leakage Current	$\text{GND} \leq V_I \leq V_{CC}$, Output Disabled	-1		$+1$	-1		$+1$	μ A
I_{OS}	Output Short Circuit Current ^[4]	$V_{CC} = \text{Max.}, V_{OUT} = \text{GND}$			-300			-300	mA
I_{CC}	V_{CC} Operating Supply Current	$V_{CC} = \text{Max.}, I_{OUT} = 0\text{ mA}, f = f_{\text{MAX}} = 1/t_{RC}$		7.5	20		6	15	mA
I_{SB1}	Automatic CE Power-down Current — TTL Inputs	Max. V_{CC} , $CE_1 \geq V_{IH}$ or $CE_2 \leq V_{IL}$, $V_{IN} \geq V_{IH}$ or $V_{IN} \leq V_{IL}$, $f = f_{\text{MAX}}$		0.1	2		0.1	1	mA
I_{SB2}	Automatic CE Power-down Current — CMOS Inputs	Max. V_{CC} , $CE_1 \geq V_{CC} - 0.3\text{V}$, or $CE_2 \leq 0.3\text{V}$, $V_{IN} \geq V_{CC} - 0.3\text{V}$, or $V_{IN} \leq 0.3\text{V}$, $f = 0$		2.5	15		2.5	15	μ A
I_{CC}	V_{CC} Operating Supply Current	$V_{CC} = \text{Max.}, I_{OUT} = 0\text{ mA}, f = f_{\text{MAX}} = 1/t_{RC}$		7.5	20		6	15	mA

Notes:


- V_{IL} (min.) = -2.0V for pulse durations of less than 20 ns.
- T_A is the "Instant On" case temperature.
- Typical values are included for reference only and are not tested or guaranteed. Typical values are an average of the distribution across normal production variations as measured at $V_{CC} = 5.0\text{V}$, $T_A = 25^{\circ}\text{C}$, and $t_{AA} = 70\text{ ns}$.
- Not more than one output should be shorted at one time. Duration of the short circuit should not exceed 30 seconds.

Electrical Characteristics Over the Operating Range (continued)

Parameter	Description	Test Conditions			62128B-55			62128B-70			Unit
					Min.	Typ. ^[3]	Max.	Min.	Typ. ^[3]	Max.	
I _{SB1}	Automatic CE Power-down Current —TTL Inputs	Max. V _{CC} , CE ₁ ≥ V _{IH} or CE ₂ ≤ V _{IL} , V _{IN} ≥ V _{IH} or V _{IN} ≤ V _{IL} , f = f _{MAX}	Com	LL		0.1	2		0.1	1	mA
I _{SB2}	Automatic CE Power-down Current —CMOS Inputs	Max. V _{CC} , CE ₁ ≥ V _{CC} − 0.3V, or CE ₂ ≤ 0.3V, V _{IN} ≥ V _{CC} − 0.3V, or V _{IN} ≤ 0.3V, f = 0	Com	LL		2.5	15		2.5	15	μA

Capacitance^[5]

Parameter	Description	Test Conditions	Max.	Unit
C_{IN}	Input Capacitance	$T_A = 25^\circ C$, $f = 1\text{ MHz}$, $V_{CC} = 5.0V$	9	pF
C_{OUT}	Output Capacitance		9	pF

AC Test Loads and Waveforms

Switching Characteristics^[6] Over the Operating Range

Parameter	Description	62128B-55		62128B-70		Unit
		Min.	Max.	Min.	Max.	
READ CYCLE						
t _{RC}	Read Cycle Time	55		70		ns
t _{AA}	Address to Data Valid		55		70	ns
t _{OHA}	Data Hold from Address Change	5		5		ns
t _{ACE}	$\overline{CE}_1$ LOW to Data Valid, CE ₂ HIGH to Data Valid		55		70	ns
t _{DOE}	$\overline{OE}$ LOW to Data Valid		20		35	ns
t _{LZOE}	$\overline{OE}$ LOW to Low Z	0		0		ns
t _{HZOE}	$\overline{OE}$ HIGH to High Z ^[7, 8]		20		25	ns
t _{LZCE}	$\overline{CE}_1$ LOW to Low Z, CE ₂ HIGH to Low Z ^[8]	5		5		ns
t _{HZCE}	$\overline{CE}_1$ HIGH to High Z, CE ₂ LOW to High Z ^[7, 8]		20		25	ns

Notes:


- Tested initially and after any design or process changes that may affect these parameters.
- Test conditions assume signal transition time of 5 ns or less, timing reference levels of 1.5V, input pulse levels of 0 to 3.0V, and output loading of the specified I_{OL}/I_{OH} and 100-pF load capacitance.
- t_{HZOE} , t_{HZCE} , and t_{HZWE} are specified with a load capacitance of 5 pF as in (b) of AC Test Loads. Transition is measured ± 500 mV from steady-state voltage.
- At any given temperature and voltage condition, t_{HZCE} is less than t_{LZCE} , t_{HZOE} is less than t_{LZOE} , and t_{HZWE} is less than t_{LZWE} for any given device.

Switching Characteristics^[6] Over the Operating Range (continued)

Parameter	Description	62128B-55		62128B-70		Unit
		Min.	Max.	Min.	Max.	
t_{PU}	$\overline{CE}_1$ LOW to Power-up, CE_2 HIGH to Power-up	0		0		ns
t_{PD}	$\overline{CE}_1$ HIGH to Power-down, CE_2 LOW to Power-down		55		70	ns
WRITE CYCLE^[9]						
t_{WC}	Write Cycle Time	55		70		ns
t_{SCE}	$\overline{CE}_1$ LOW to Write End, CE_2 HIGH to Write End	45		60		ns
t_{AW}	Address Set-up to Write End	45		60		ns
t_{HA}	Address Hold from Write End	0		0		ns
t_{SA}	Address Set-up to Write Start	0		0		ns
t_{PWE}	$\overline{WE}$ Pulse Width	45		50		ns
t_{SD}	Data Set-up to Write End	25		30		ns
t_{HD}	Data Hold from Write End	0		0		ns
t_{LZWE}	$\overline{WE}$ HIGH to Low Z ^[8]	5		5		ns
t_{HZWE}	$\overline{WE}$ LOW to High Z ^[7, 8]		20		25	ns

Data Retention Characteristics (Over the Operating Range for “LL” version only)


Parameter	Description			Conditions ^[10]	Min.	Typ.	Max.	Unit
V_{DR}	V_{CC} for Data Retention				2.0			V
I_{CCDR}	Data Retention Current	Ind.'l	LL	$V_{CC} = V_{DR} = 3.0V$, $CE_1 \geq V_{CC} - 0.3V$, or $CE_2 \leq 0.3V$, $V_{IN} \geq V_{CC} - 0.3V$ or, $V_{IN} \leq 0.3V$		1.5	15	μA
I_{CCDR}	Data Retention Current	Com.	LL	$V_{CC} = V_{DR} = 3.0V$, $CE_1 \geq V_{CC} - 0.3V$, or $CE_2 \leq 0.3V$, $V_{IN} \geq V_{CC} - 0.3V$ or, $V_{IN} \leq 0.3V$		1.5	15	μA
$t_{CDR}^{[3]}$	Chip Deselect to Data Retention Time				0			ns
$t_R^{[3]}$	Operation Recovery Time				70			ns

Switching Waveforms
Read Cycle No.1^[11, 12]

Notes:


9. The internal write time of the memory is defined by the overlap of $\overline{CE}_1$ LOW, CE_2 HIGH, and $\overline{WE}$ LOW. $\overline{CE}_1$ and $\overline{WE}$ must be LOW and CE_2 HIGH to initiate a write, and the transition of any of these signals can terminate the write. The input data set-up and hold timing should be referenced to the leading edge of the signal that terminates the write.
10. No input may exceed $V_{CC} + 0.5V$.
11. Device is continuously selected. $\overline{OE}$, $\overline{CE}_1 = V_{IL}$, $CE_2 = V_{IH}$.
12. $\overline{WE}$ is HIGH for read cycle.

Switching Waveforms (continued)

Read Cycle No. 2 ($\overline{OE}$ Controlled)^[12, 13]



Write Cycle No. 1 ($\overline{CE}_1$ or CE_2 Controlled)^[14, 15]




Notes:


13. Address valid prior to or coincident with $\overline{CE}_1$ transition LOW and CE_2 transition HIGH.
14. Data I/O is high impedance if $\overline{OE} = V_{IH}$.
15. If $\overline{CE}_1$ goes HIGH or CE_2 goes LOW simultaneously with $\overline{WE}$ going HIGH, the output remains in a high-impedance state.

Switching Waveforms (continued)

Write Cycle No. 2 ($\overline{WE}$ Controlled, $\overline{OE}$ HIGH During Write)^[14, 15]



Write Cycle No.3 ($\overline{WE}$ Controlled, $\overline{OE}$ LOW)^[14, 15]



Note:

16. During this period the I/Os are in the output state and input signals should not be applied.



Truth Table


CE ₁	CE ₂	OE	WE	I/O ₀ –I/O ₇	Mode	Power
H	X	X	X	High Z	Power-down	Standby (I _{SB})
X	L	X	X	High Z	Power-down	Standby (I _{SB})
L	H	L	H	Data Out	Read	Active (I _{CC})
L	H	X	L	Data In	Write	Active (I _{CC})
L	H	H	H	High Z	Selected, Outputs Disabled	Active (I _{CC})

Ordering Information


Speed (ns)	Ordering Code	Package Name	Package Type	Operating Range
55	CY62128BLL-55SI	S34	32-Lead 450-Mil SOIC	Industrial
	CY62128BLL-55SC	S34	32-Lead 450-Mil SOIC	Commercial
	CY62128BLL-55ZI	Z32	32-Lead TSOP Type I	Industrial
	CY62128BLL-55ZAI	ZA32	32-Lead STSOP Type I	Industrial
	CY62128BLL-55ZRI	ZR32	32-Lead Reverse TSOP Type I	Industrial
70	CY62128BLL-70SI	S34	32-Lead 450-Mil SOIC	Industrial
	CY62128BLL-70SC	S34	32-Lead 450-Mil SOIC	Commercial
	CY62128BLL-70ZI	Z32	32-Lead TSOP Type I	Industrial
	CY62128BLL-70ZC	Z32	32-Lead TSOP Type I	Commercial
	CY62128BLL-70ZAI	ZA32	32-Lead STSOP Type I	Industrial

Package Diagrams

32-Lead (450 Mil) Molded SOIC S34





32-Lead Thin Small Outline Package Type I (8x20 mm) Z32




Package Diagrams (continued)

32-Lead Shrunken Thin Small Outline Package (8x13.4 mm) ZA32



51-85094-*D

32-Lead Reverse Thin Small Outline Package ZR32



51-85089-*C

All product and company names mentioned in this document are the trademarks of their respective holders.



Document History Page

Document Title: CY62128B MoBL [®] 128K x 8 Static RAM Document Number: 38-05300				
REV.	ECN NO.	Issue Date	Orig. of Change	Description of Change
**	116566	06/20/02	DSG	Changed from Spec number: 38-00524 to 38-05300
*A	126601	06/09/03	JUI	Changed CE to CE ₁ and added CE ₂ ≤ 0.3V in Data Retention Characteristics table Removed these part numbers from Ordering Information table: CY62128BLL-55ZC, CY62128BLL-55ZAC, CY62128BLL-55ZRC, CY62128BLL-70ZAC, CY62128BLL-70ZRI, CY62128BLL-70ZRC