

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

2000.

BY AMP INCORPORATED.

ALL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN

MATED WITH:
PASSEND ZU:

BG6

LOC

DIST

REVISIONS

AENDERUNGEN

DESCRIPTION

BESCHREIBUNG

DATE

DWN

APVD

PROJEKT NR.

C8

text for packaging corrected ECR-08-001868

22.01.08

SR

ST

Screw version

Thermo

1

2

M3x10

77.5

83.5

1

212

34

27

33

Crimp version

1

3

M3x10

77.5

83.5

spring clamp version

4

1

M3x10

77.5

83.5

assembly directions

Sti

Bu

19.5 x

distance for a safe contact max: max: 21 mm

Contact arrangement

view from termination side

Printing 1-16 Thermo

1+ 2+ 3+ 4+ 5+ 6+ 7+ 8+

9- 10- 11- 12- 13- 14- 15- 16-

Printing 17-32 Screw

17 18 19 20 21 22 23 24

25 26 27 28 29 30 31 32

Printing 1-16 Screw

1 2 3 4 5 6 7 8

9 10 11 12 13 14 15 16

Printing 8+4+4 Screw/Thermo

1 2 3 4 5+ 6+ 7+ 8+

9 10 11 12 13- 14- 15- 16-

NOTES:

1 SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM

2 SUITABLE HOOD SIZE 6; 10: SERIES HB; HD;HIP;EMV
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264

3 Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm

4 STANDARDS:
DIN EN 61984; DIN EN 60664-1

5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED

6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 200 PIECES

Panel cut-out for contact insert

when used without housing

70.5

27

20

36

77.5

85.5

				1	1						cover spring clamp version		light grey	4		
						1	1				cover crimp version		light grey	3		
1	1	1	1					1	1	1	cover screw version		light grey	2		
1	1	1	1	1	1	1	1	1	1	1	pin insert		light grey	1		
0-19-4	1-89-5	7-97-1	2-92-3	1-9	1-7	1-1					DESCRIPTION	MATERIAL	COLOR	ITEM NO. POS.	NOTES	
HE.16.Sti.S.B 1-16.KM	HE.16.Sti.S.B.17-32-AU	HE.16.Sti.S-T.B 8+4+4	HE.16.Sti.S.B.1-16-AU	HE.16.Sti.S.C.B 17-32	HE.16.Sti.S.C.B 1-16	HE.16.Sti.C.B 17-32	HE.16.Sti.C	HE.16.Sti.S.B 17-32	HE.16.Sti.S-T.B 1-16	HE.16.Sti.S.B 1-16	ORDERING TEXT	DWN Schneider 08.02.99	CHK Schweiger 08.02.00	APVD -	NAME HTS Elektrotechnik 53819 Neunkirchen, Germany	
											DIMENSIONS: DIMENSIONEN: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN				
											1 ISO 8015					
											2 ISO 2768 - mH - E					
											3 DIN 16901 - 140					
											0 PLC					
											1 PLC					
											2 PLC					
											3 PLC					
											ANGLES / WINKEL					
											FINISH / OBERFLÄCHE / FARBE					
											MATERIAL					
											APPLICATION SPEC. VERARBEITUNGSSPEZ.					
											WEIGHT GEWICHT					
											CUSTOMER DRAWING /KUNDENZEICHNUNG					
											SCALE MASSSTAB 1:1					
											SHEET BLATT 1 OF VON 1					
											REV C8					

AMP 1471-9 REV 27JUN96

This is a TRANSLATED file from Computervision, Inc., Medusa Revision 12.2.5T